




ISO 4029

DIN 916



BN 621

Hex socket set screws

with cup point

Stainless steel A2

- ~UNI 5929

Article#	d ₁	d ₂	s	t min.	L
1236482	M1,6	0,55-0,8	0,7	1,5	2,5
1236490					3
1236504					4
1236512					5
1236520					6
1236539	M2	0,75-1	0,9	0,8	2,5
1236547				1,7	3
1236555					4
1236563					5
1236571					6
1236598					8
1423649					10
1236601	M2,5	0,95-1,2	1,3	1,2	3
1236628				2	4
1236636					5
1236644					6
1236652					8
1423657					10
1423746					12
1114875	M3	1,15-1,4	1,5	1,2	3
1114883					4
1114891				2	5
1114905					6
1114913					8
1114921					10
1423754					12

Article#	d ₁	d ₂	s	t min.	L
1423800	M3	1,15-1,4	1,5	2	16
1423908					20
3059844					25
3059845					30
1114948	M4	1,75-2	2	1,5	4
1114956					5
1114964				2,5	6
1114972					8
1114980					10
1114999					12
1706357					(14)
1424033					16
1424092					20
1424106					25
1424815					30
3059846					35
3059847					40
1115006	M5	2,25-2,5	2,5	2	5
1115014				3	6
1115022					8
1115030					10
1115073					12
1706403					(14)
1115081					16
1424823					20
1424831					25
1424858					30
1424866					35
1424874					40
1115103	M6	2,75-3	3	2	6
1115111				3,5	8
1115138					10
1115146					12
1716956					(14)
1115189					16
1115235					20
1424882					25
1424890					30
1424904					35
1424912					40
1424920					45

Article#	d ₁	d ₂	s	t min.	L
1424939	M6	2,75-3	3	3,5	50
1115251	M8	4,7-5	4	3	8
1115308				5	10
1115324					12
1115359					16
1115375					20
1115413					25
1424947					30
1424955					35
1424963					40
1424971					45
1424998					50
1115421	M10	5,7-6	5	4	10
1115448				6	12
1115456					16
1115464					20
1115472					25
1425005					30
1425013					35
1425021					40
1425048					45
1425056					50
3092247					60
1425064	M12	7,64-8	6	4,8	12
1425072				8	16
1425080					20
1425099					25
1425102					30
1425110					35
1425129					40
1425137					45
1425145					50