

Tools That Work





BONDHUS Balldriver® L-wrenches


Precision Chamfer Tips and High Quality Machining:

- Fast insertion and full tool engagement in the screw head
- Extended tip life
- Reduced fastener wear
- Smooth rotational action

Balldriver® Tip



- **Exclusive Bondhex™ locking tool case** keeps tools organized and prevents loose or lost hex keys
- **Angle entry to 25°** works efficiently even near obstructions



Balldriver® L-wrench Sets

Item no.	Description	List each
10936	12 Pc Set .050-5/16"	
10937	13 Pc Set .050-3/8"	
10999	9 Pc Set 1.5-10mm	

Double Pack Sets



Double Pack and Multi-pack Sets

Item no.	Description	List Each
20199	22 Pc Double Pack Set Balldriver® L-wrench 1.5-10mm & .050-3/8"	
14189	22 Pc Multi Pack Set Balldriver® L-wrench .050-3/8" GorillaGrip® Hex Fold Up 5/64-1/4"	

ProHold® Balldriver® L-wrench Sets

- ProHold® Tip holds screws tight **FIRST TIME - EVERY TIME**
- Patented ProHold® Tip technology means never dropping a screw again
- Allows for maximum torque without distortion of ProHold® button
- Non-magnetic technology
- Balldriver® Tip for angle entry to 25° and fast screw removal




Item no.	Description	List each
74938	10 Pc Set 1/16-1/4"	
74937	13 Pc Set .050-3/8"	
74992	7 Pc Set 1.5-6mm	
74999	9 Pc Set 1.5-10mm	
20499	22 Pc Double Pack ProHold® Set 1.5-10mm & .050-3/8"	

Single tools available

GoldGuard™ and BriteGuard™ Balldriver® L-wrenches



GoldGuard™
FINISH



- Easy identification Inch/Metric
Silver = Inch, Gold = Metric
- Easier to read size even in small sizes

- Corrosion resistant
- Attractive, professional quality, easy to clean

- Balldriver® Tip for angle entry to 25°



BriteGuard™
FINISH

Bondhus GoldGuard™ Balldriver® L-wrench Sets

Item no.	Description	List each
37937	13 Pc Inch .050-3/8"	
38099	9 Pc Metric 1.5-10mm	
20899	22 Pc Double Pack GoldGuard™ Finish .050-3/8" & 1.5-10mm	
26937	13 Pc Inch .050-3/8"	
20399	22 Pc Double Pack BriteGuard™ & GoldGuard™ Finishes Silver .050-3/8" & Gold 1.5-10mm	

Stubby Balldriver® L-wrenches



- Smaller inside radius for tight spaces
- Allows for lower clearance
- Balldriver® Tip on long arm for angle entry to 25° and fast screw removal

Item no.	Description	List each
16537	13 Pc Inch .050-3/8"	
16599	9 Pc Metric 1.5-10mm5	
20599	22 Pc Double Pack .050-3/8" & 1.5-10mm	

- Low profile short arm allows entry into tight spots
- Precision cut tip for better screw engagement



GorillaGrip® Fold-ups

Handle is 40% stronger than steel handles

- **Speed Wrench Feature**
90° stop converts the tool into a non-stop, timesaving, speed wrench
- **Turn & Flip Feature**
No repositioning the tool when working against obstructions

Color Coded

- Inch
- Metric
- Star
- Inch/Metric



- **Patented Flutes**
allow for easy selection of one tool at a time

Item no.	Description	List each
12550	12 Pc Combo 5/64-5/32" & 1.5-5mm	
12585	5 Pc Hex Inch 3/16-3/8"	
12587	7 Pc Hex Metric 2-8mm	
12589	9 Pc Hex Inch 5/64-1/4"	
12591	9 Pc Hex Inch .050-3/16"	
12592	7 Pc Hex Metric 1.5-6mm	
12595	6 Pc Hex Metric 3-10mm	
12632	8 Pc Star T6-T25	
12634	8 Pc Star T9-T40	
12894	5 Pc Ballpoint 3/16-3/8"	
12897	5 Pc Ballpoint 5-10mm	


Single tools available





Cushion Grip T-Handles

- Welded handle gives unmatched strength and durability
- Ergonomic, Cushion Grip T-handle for safety & comfort
- Heavy duty handle generates a flywheel effect for super fast insertion or removal of screws



Straight Hex

Balldriver® Tip

ProHold® Balldriver® Tip

Star Tip

ProHold® Star Tip



- Available in pouch or with stand



Bondhus T-handles Sets

Bondhus Balldriver® T-handle Hex Sets - Graduated Length

Item no.	Description	List each
13138	10 Pc Inch 3/32-3/8" in Pouch	
13190	10 Pc Inch 3/32-3/8" with Stand	
13187	8 Pc Metric 2-10mm in Pouch	
13189	8 Pc Metric 2-10mm with Stand	

Bondhus T-handle Hex Sets (6" Length) in Pouch

Item no.	Description	List each
15238	10 Pc Inch 3/32-3/8"	
15287	8 Pc Metric 2-10mm	

Bondhus T-handle Hex Sets (6" Length) with Stand

Item no.	Description	List each
15290	10 Pc Inch 3/32-3/8"	
15289	8 Pc Metric 2-10mm	

Bondhus Star T-handle Hex Sets (Graduated Length) with Stand

Item no.	Description	List each
33034	8 Pc Star T9-T40	

Screwdriver Sets



Balldriver® Tip



ProHold® Balldriver® Tip



Star Tip



ProHold® Star Tip

- ComfortGrip handles designed for maximum torque with unrivaled comfort & grip
- Gives you a tight grip even with wet or oily hands
- Balldriver® Tip for angle entry to 25° and fast screw removal



Bondhus Screwdriver Sets

Bondhus Balldriver® Screwdriver Sets

Item no.	Description	List each
10632	8 Pc Set .050-5/32"	
10637	13 Pc Set .050-3/8"	
10686	6 Pc Set 1.5-5mm	
10699	9 Pc Set 1.5-10mm	

Bondhus ProHold® Balldriver® Screwdriver Sets

Item no.	Description	List each
74632	8 Pc Set .050-5/32"	
74637	13 Pc Set .050-3/8"	
74686	6 Pc Set 1.5-5mm	
74699	9 Pc Set 1.5-10mm	

Bondhus Star Screwdriver Sets

Item no.	Description	List each
34532	8 Pc Set T6-T25	
34534	8 Pc Set T9-T40	

Bondhus ProHold® Star Screwdriver Set

Item no.	Description	List each
75534	8 Pc Set T9-T40	

Single tools available

Ergonic Screwdrivers



NEW!

The first handle that
actually molds to
your hand!


- No pressure points, no strain
- High torque transmission

- Flexible handle core fits perfectly into your hand at all times



- Scratch resistant
- Black tip for precision fit
- Blades manufactured from chrome-molybdenum-vanadium steel

1. Blade is injection molded with impact proof hard plastic.
2. Handle core is coated with elastic, elastomer containing cells of highly flexible plastics.
3. Unique, ERGONIC screwdriver handle from Felo



Available in VDE Insulated!

Item no. 53167

List each

Description 6 Pc Ergonic Slotted/Phillips
Screwdriver Set

Slotted: 1/8, 5/32, 7/32, 1/4"

Phillips: PH1, PH2

Item no. 53173

List each

Description 3 Pc Ergonic Slotted/Phillips
Screwdriver Set

Slotted: 7/32, 1/4"

Phillips: PH2

Heavy Duty Screwdrivers



- Metal cap prevents damage when struck
- Hexagon blades manufactured from chrome-molybdenum-vanadium steel for extra torque
- Hex collar allows use of wrench for extra leverage
- Comfortable, two-component, soft grip handle for high torque
- Anti-roll handle design
- Black tip for precision fit



5 Pc Heavy Duty "Chisel" Screwdriver Set

Item no. 50707


List each

Description 5 Pc Slotted/Phillips Set

Slotted: 3/16, 7/32, 1/4"

Phillips: PH1, PH2

Felo Screwdrivers



- Comfortable, two-component, soft grip handle for high torque
- Ergonomically refined design
- Hanging hole for easy storage or increased torque
- Anti-roll handle design
- Blades manufactured from chrome-molybdenum-vanadium steel
- Black tip for precision fit



6 Pc Screwdriver Set

Item no. 50174

List each

Description 6 Pc Slotted/Phillips Set

Slotted: 9/64, 5/32, 7/32, 1/4"

Phillips: PH1, PH2



Single tools available



8 in 1 Screwdriver Bit Holder Sets



- Easy to reach bits store inside the handle
- Soft grip 2-component handle for strength, comfort and excellent torque transmission
- Bits are held securely in individual slots of magazine by powerful magnet
- Ergonomic design for comfort even during heavy use



**Fits
all 1/4"
bits**

Stubby Bit holder with stainless steel sleeve and extremely strong magnet



Item no.	52227	List each
Bits Included	Slotted: 3/16, 7/32, 1/4"	
	Phillips: PH0, PH1, PH2 Pozidriv: PZ1, PZ2	
Item no.	52769	List each
Bits Included	Slotted: 7/32, 1/4"	
	Phillips: PH1, PH2 Square: SQ0, SQ1, SQ2, SQ3	

Professional Reversible Ratchet Bit Holder




Item no.	52223	List each
Bits Included	Slotted: 3/16, 7/32, 1/4"	
	Phillips: PH0, PH1, PH2 Pozidriv: PZ1, PZ2	
Item no.	52767	List each
Bits Included	Slotted: 7/32, 1/4"	
	Phillips: PH1, PH2 Square: SQ0, SQ1, SQ2, SQ3	

Felo Flexible Bit holder

Item no.	50570
List each	
Description	Flexible 1/4" Magnetic Bit Holder

Flexible Shaft!



- Comfortable soft grip handle
- Hanging hole for easy storage or increased torque
- Braided cable prevents loading in either direction

Felo Star Bit Sets

- Incredible screw holding power for true one-handed operation
- Bit holder with automatic adjustment to depth of screw head
- Allows quick and easy bit replacement

Item no.	53015	List each
Bit Holder	Felo Star Bit Holder	
Bits Included	Slotted: 7/32, 1/4"	
	Phillips: PH2, PH3	
	Square: SQ2, SQ3	
	Torx®: T20, T25	



Item no.	53527	List each
Bit Holder	Felo Star Bit Holder	
TiN Bits Included	Slotted: 7/32, 1/4" Phillips: PH2, PH3	
	Torx®: T20, T25, T30, T40	



- Bit holder securely holds screw

e-pro

11 in 1 Multi-Bit Insulated Screwdriver with 1/4" Bits



- 1/4" Bits manufactured from long-lasting, high quality steel
- Each insulated bit holder is individually tested to 10,000 volts
- Conforms to VDE international standards
- Soft grip, ergonomic 2-component handle
- Handy, molded storage case



Item no.	51427
List each	
Bit Holder	Felo Bit Holder
Bits Included	Slotted: 1/8, 5/32, 7/32, 9/32"
	Phillips: PH0, PH1, PH2
	Pozidriv: PZ1, PZ2
	Torx®: T15, T20

Felo E-smart Insulated Sets

- 2 sets in 1 offers 24 different combinations with most popular sizes
- 12 piece 1000 Volt insulated screwdriver set in handy metal storage box
- Each blade individually tested to 10,000 Volts
- Rotating cap turns blades into 12 Precision drivers



Item no.	53077
List each	
Includes:	2 Component Handle, Precision Cap and Handy Storage box
Sizes Included	
Slotted:	3/32, 1/8, 9/64, 5/32, 7/32, 1/4"
Phillips:	PH1, PH2 Pozidriv: PZ2
Torx®:	T10, T15, T20

Item no.	53477
List each	\$
Includes:	2 Component Handle, Precision Cap and Handy Storage box
Sizes Included	
Slotted:	3/32, 1/8, 9/64, 5/32, 7/32, 1/4"
Phillips:	PH1, PH2
Square:	SQ0, SQ1, SQ2, SQ3



Felo Insulated Screwdrivers



- Comfortable, soft grip outer material for highest torque
- Hanging hole for easy storage or increased torque
- 1,000 Volt Insulated Screwdriver, individually tested to 10,000 Volts
- Ergonomic, anti-roll handle design
- Blades manufactured from chrome-molybdenum-vanadium steel
- Black tip for precision fit



- GS tested for safety

Item no.	50176
List each	
Description	6 Pc Slotted/Phillips Set
	Slotted: 1/8, 9/64, 5/32, 7/32"
	Phillips: PH1, PH2



Smart Screwdriver Sets



Smart Combination Handle
T-Handle & Screwdriver
in one!

- Interchangeable Sets include 2-component Smart Combination T & Screwdriver handle
- Wide variety of tips and sockets means the right tool set for the job
- Extra strong, chrome-molybdenum-vanadium steel
- Blades with precision fit black tip



Item no.	50630	List each
Includes:	Smart Combination handle and blades	
Slotted:	5/32, 1/4"	Phillips: PH1, PH2
Hex:	7/64, 1/8, 9/64, 5/32, 3/16, 1/4"	
Hex:	3mm, 4mm, 5mm, 6mm	
Torx®:	T6, T7, T8, T9, T10, T15, T20, T25, T30, T40	

Item no.	52949	List each
Includes:	Smart Combination handle, bits and blades	
1/4" Bit Holder & Bits:	Slotted: 9/64, 3/16, 1/4"	
Phillips:	PH1, PH2, PH3	Hex: 3/16, 1/4"
Pozidriv:	PZ1, PZ2, PZ3	Torx®: T15, T20, T25, T30, T40
1/4" Adapter & Sockets:	3/16, 7/32, 1/4, 9/32, 5/16, 3/8, 1/2"	
3" socket extension,	1/4" ratchet,	1/4" extension

High Quality Bits

- Superior hardness and torque
- High quality steel for heavy duty use, ISO 9001 certified
- Precision fit achieved by profilated, not pressed, bits
- Complete range of sizes, lengths and tips



Professional Quality Pliers



- Ergonomically refined design for maximum comfort
- 2-component handle technology
- Optimum long-lasting corrosion protection from special matt chromium surface
- Drop-forged from special steel
- Induction hardened cutting edge (60-64 HRC)

Item no. 50022
List each
7" Comfort Grip
Combination Pliers


More pliers available

Item no. 53649

List each
Lineman's Pliers



Felo Insulated Pliers



- Insulated to 1000V
- Ergonomically refined design for maximum comfort
- 2-component handle technology
- Optimum long-lasting corrosion protection from special matt chromium surface
- Drop-forged from special steel
- Induction hardened cutting edge (60-64 HRC)



www.bondhus.com

Bondhus, Balldriver, Bondhex, GoldGuard, BriteGuard, ProGuard, Protanium and GorillaGrip are trademarks of Bondhus Corporation. ©2008 Bondhus Corp Item#97196

Torque Limiting Handle with 1/4" Bit Holding Blade

0.6 - 1.5 Nm
5 - 13 in/lb.

1.5 - 3.0 Nm
13 - 26 in/lb.

3.0 - 5.4 Nm
26 - 48 in/lb.



- Colored ring indicates torque range



- Precise, easy adjustment of torque
- Precise release indicated by acoustic and mechanical signal
- Comfortable, two-component, soft grip handle
- Interchangeable chrome-molybdenum-vanadium blades
- Black tip for precision fit

Felo Precision Screwdrivers

- Ergonomic soft grip handle designed for precision work
- Freely rotating cap for minimal friction
- Hanging hole for easy storage or inserting lever
- Full length polypropylene core
- Anti-roll handle design
- Blades manufactured from chrome-molybdenum-vanadium steel
- Black tip for precision fit



Item no. 31844

List each

Description

6 Pc Slotted/Phillips Set
Slotted: 1/16, 5/64, 3/32, 1/8"
Phillips: PH00, PH0
Handy storage box included

