

## Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
  - Favorite Products List
  - Locate Distributor

## Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) [Search Tips](#) 

 **Text Search: 'FZOE3-10M10'**

Your search criteria matched only one product, shown below

## FZOE3-10M10



- Patch cords are tested to support network transmission speeds up to 10 Gb/s for link lengths up to 550 meters with an 850nm source per IEEE 802.3ae 10 GbE standard
  - Pass all TIA/EIA-568-B.3 performance requirements
  - Insertion loss per connection: 0.10dB typical; 0.30dB maximum
  - Backward compatible for use with all 50/125µm system requirements
  - Factory terminated and 100% tested for insertion loss
  - Insertion loss data recorded for every multimode patch cord
  - Lifetime traceability of test data to a Q.C. number on each patch cord
  - SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
  - Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber
- \*Additional lengths and availability: Patch cords are available in 1 – 10 meter lengths in 1 meter increments, and 15, 20, 25 and 30 meter lengths. Pigtails are available in 1, 2, and 3 meter lengths. Ex: To order lengths other than 1 meter, replace the 1 after the M (FZPE10-10M1) with the desired length (FZPE10-10M2 for 2 meter length). The above lengths are stock items. For

other lengths, contact Customer Service for actual lead times.

|                                |                                                                                                 |
|--------------------------------|-------------------------------------------------------------------------------------------------|
| ▪ Part Number                  | FZOE3-10M10                                                                                     |
| ▪ RoHS Compliancy Status       | RoHS directive is not applicable                                                                |
| ▪ Note                         | Intended for use in fixed installations which are outside the scope of RoHS                     |
| ▪ Part Description             | SC to LC Patch Cord, Optimized OM4, RISER, 0.15 dB IL Loss, Duplex, 1.6mm jacketed cable – 10m. |
| ▪ Product Type                 | Hybrid Patch Cords                                                                              |
| ▪ Length (m)                   | 10                                                                                              |
| ▪ Fiber Compatibility          | 10 GbE 50/125µ                                                                                  |
| ▪ Fiber Cable Size             | 1.6mm                                                                                           |
| ▪ Fiber Cable Type             | Jacketed Cable                                                                                  |
| ▪ Fiber Type                   | Multimode                                                                                       |
| ▪ Connector 1 Type             | SC Connector                                                                                    |
| ▪ Connector 2 Type             | LC Connector                                                                                    |
| ▪ End Configurations           | SC to LC                                                                                        |
| ▪ Fiber Count                  | 2                                                                                               |
| ▪ Flammability Rating          | Riser (OFNR)                                                                                    |
| ▪ Pricing Description          | SC to LC, Optimized OM4, RISER, Duplex, 1.6mm jacketed cable, 10M                               |
| ▪ Min. Order UOM               | PC                                                                                              |
| ▪ Min. Order Qty.              | 1                                                                                               |
| ▪ BOM Qty. (# of Pkgs.)        | <input type="text" value="0"/>                                                                  |
| ▪ Add to Favorite Product List | <input type="button" value=""/>                                                                 |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.