


D-SUBMINIATURE CONNECTORS: K66X Series Right Angle PCB Mount

K66X Series Dimensions Dimensions in mm



Shell Size	A	B	C	C1	D	E
In mm	±.015 ±0.38	±.005 ±0.13	±.010 ±0.25	±.010 ±0.25	±.005 ±0.13	±.005 ±0.13
15 (E)	1.213 30.81	.984 24.99	.643 16.33	.666 16.92	.090 2.29	.010 0.25
26 (A)	1.541 39.14	1.312 33.32	.971 24.66	.994 25.25	.090 2.29	.020 0.51
44 (B)	2.088 53.04	1.852 47.04	1.511 38.38	1.534 38.96	.090 2.29	.020 0.51
62 (C)	2.729 69.32	2.500 63.50	2.159 54.84	2.182 55.42	.095 2.41	.023 0.58

C = Exterior of Female Shell (S)
C1 = Interior of Male Shell (P)

Electrical Characteristics

Rated Current: 1.5A
Rated Voltage: 29Vac



Generated Part Number

K66X-E15P-N

Part Number Builder

K66X	-	E15	P	N	
Series		Shell Size Contact	Contact Type	Mounting Option	Plating Option

Series

K66X - High Density D-Subminiature Connector,
Right Angle PCB Termination, 0.350" Footprint

Shell Size-Contact Option

E - 15 Contacts
A - 26 Contacts
B - 44 Contacts
C - 62 Contacts

Contact Type

P - Pin Contact (Plug)
S - Socket Contact (Receptacle)

Mounting Option

N - With Boardlocks and #4-40 UNC Threaded Inserts
NJ - With Boardlocks and #4-40 Jackscrews Installed

Plating Option

Blank - Gold Flash
30 - 30µ" Gold