

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0848547026

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

DeviceNet Micro-Change Single-Ended Cordset, 5 Poles, Female (Straight) to Pigtail, NMEA 2000 Style Cable, 5.0m (16.40') Length, meets NMEA 2000

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Industrial Cordsets

Series

84854

Connector End A

Micro-Change (M12)

Connector End B

Pigtail

IP Rating

IP67

Material - Contact

Copper Alloy

Overview

Brad Micro-Change (M12) Connectors

Product Name

Micro-Change (M12)

Protocol

N/A

Region

Europe

Type

Single Ended

UPC

822350909242

Physical

Cable Diameter

5.72mm (.225")

Cable Length

5.0m (16.40')

Color - Cable Jacket

Gray

Coupling Style

Threaded

Gender

Female-Pigtail

Keyway

Single

LED Indicator

No

Material - Cable Jacket

PVC

Material - Connector Body

PVC

Material - Coupling Nut

Nickel-plated Brass

Material - Plating Mating

Gold

Orientation

Straight to Pigtail

Poles

5

Temperature Range - Operating

-20°C to +105°C

Wire Size AWG

22

Wire/Cable Type

Thin Standard Cable

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

250V

Material Info

Engineering Number

NMEA-DND20NB-M050

Reference - Drawing Numbers

Sales Drawing

SD-84854-022



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

84854 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION