







ASSEMBLY - VIEW FROM TOP




ASSEMBLY - VIEW FROM SIDE



ASSEMBLY - VIEW FROM BOTTOM



ISOMETRIC VIEW



SECTION A-A

1580T10**
Finish - Sides - Black Painted Steel
Case - Aluminum Extrusion
Rated - 120 VAC, 60 Hz, 15 Amps
Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)
- UL Listed, Standard UL1363
Cord Length
1580T10A1 - 6' Foot Power Cord (NEMA 5-15P)
1580T10B1 - 15' Foot Power Cord (NEMA 5-15P)

