

Tous droits réservés. Toute réimpression ou utilisation non autorisée sans la permission écrite de la FCI est formellement interdite.
All rights reserved. Any reprinting or unauthorized use without the written permission of FCI is expressly prohibited.




PRODUCT NUMBER

71600-YXXLF


- LEAD FREE, SEE NOTE 6 & 7.
- TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2
- OPTIONAL STRAIN RELIEF
SEE SHEET 2

TRIANGLE INDICATES
POSITION 1
NOTE 5




NOTES:

- 1 - PLASTIC MAT'L : GLASS FILLED HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: GREY
- 2 - PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PRODUCT PACKAGED IN TUBES.
- 4 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS
EXAMPLE : 8 POS N x 2.54 = 20.32mm
- 5 - 2x5, 2x6, 2x7 HAVE NO LEFT POLARIZING SLOT.
- 2x2, 2x3 WITH CENTRAL KEY HAVE NO TRIANGLE, NO LEFT AND RIGHT POLARIZING SLOT.
- 2x2 WITHOUT CENTRAL KEY HAS NO LEFT AND RIGHT POLARIZING SLOT.
- 2x3, 2x4 WITHOUT CENTRAL KEY HAVE NO LEFT POLARIZING SLOT
- 2x4 WITH CENTRAL KEY HAVE NO LEFT AND RIGHT POLARIZING SLOT
- 6 - 71600-XXXLF IS SIMILAR TO 71600-XXX, THE SUFFIX 'LF' IS ADDED FOR LEAD FREE IDENTIFICATION.
- 7 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008.
PACKAGING SPECIFICATION AS PER GS-14-920.



COVER ORIENTATION



D-D SECTION

mat'l. code SEE NOTES				tolerances unless otherwise specified			CUSTOMER COPY	FCI ELECTRONICS www.fciconnect.com	
litr	ecr no	dr	date		X.X ±0.3				
AG	F04-0330	LMU	04.09.01	linear	X.XX ±0.13		projection	title QUICKIE III FEM 0.76µm Au	
AH	F05-0109	JCO	05.01.17		X.XXX ±0.05				
AJ	F05-0171	LMU	05.04.07	angles				product family 2.54MM IDC	
AK	F05-0180	LMU	05.04.22	dr	D.LE	01.01.24			
				enr	P.NZ	01.01.24		size dwg no	
AE	F03019	DLE	03.01.23	chr	JF.N	01.01.24			
AF	F04-0168	LMU	04.04.08	appd	P.NZ	01.01.24		A3 71600	
sheet	revision	AK	AC				scale		
index	sheet	1	2				5:1	code 213 sheet 1 of 2	

Tous droits réservés. Toute réimpression ou utilisation non autorisée sans la permission écrite de la FCI est formellement interdite. Toute réimpression ou utilisation non autorisée sans la permission écrite de la FCI est formellement interdite.


All rights reserved. Reproduction or use in any form without the written permission of FCI is expressly prohibited. All rights reserved. Reproduction or use in any form without the written permission of FCI is expressly prohibited.




CORE RANGE	
STRAIN RELIEF	Nbr OF POSITIONS
0/1	04
0/1	06
0/1	08
0/1	10
0/1	14
0/1	16
0/1	18
0/1	20
0/1	24
0/1	26
0/1	30
0/1	34
0/1	40
0/1	50
0/1	60
0/1	64
PLATING 0.76µm GOLD ON CONTACT AREA 1.27 µm Ni REMAINDER OF PRODUCT	

CATALOGUE RANGE	
STRAIN RELIEF	Nbr OF POSITIONS
2/6	04
2/6	06
2/6	08
2/6	10
2/6	14
2/6	16
2/6	18
2/6	20
2/6	24
2/6	26
2/6	30
2/6	34
2/6	40
2/6	50
2/6	60
2/6	64
PLATING 0.76µm GOLD ON CONTACT AREA 1.27 µm Ni REMAINDER OF PRODUCT	


624
304
204 / 224
004
DASHES NOT AVAILABLE




WITHOUT STRAIN RELIEF




WITH LOW PROFILE STRAIN RELIEF




WITH STANDARD STRAIN RELIEF



WITH LATCHING STRAIN RELIEF



71600-6YY	●					●
71600-3YY		●	●			
71600-2YY	●				●	
71600-1YY	●					
71600-0YY	●		●			
PRODUCT NUMBER	WITH	WITHOUT	STANDARD	WITHOUT	LOW PROFILE	LATCHING
	CENTRAL KEY		STRAIN RELIEF			

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		 ELECTRONICS www.fciconnect.com						
ltr	ecn no	dr	date	linear				projection 	title IDC RECEPT DR						
X	F70666	AAN	97.11.05												
Y	F10121	DLE	01.01.24												
AA	F10199	GCO	01.04.26	angles					product family QUICKIE				code 213		
AB	F03019	DLE	03.01.23	dr	D.LE	01.01.24									
AC	F05-0180	LMU	05.04.22	enrg	P.NZ	01.01.24									
				chr	JF.N	01.01.24	scale N/A	size A3		dwg no 71600				sheet 2 of -	
				appd	P.NZ	01.01.24									
sheet index		revision sheet													