




2.54±0.20

Recommended P.C.Board
Hole Layout



Specifications

Current Rating: 3Amp

Insulation Resistance: 1000MΩ Min.

Dielectric Withstanding: 600V AC

Contact Resistance: 20mΩ Max.

Operating Temperature: -40°C to +105°C

Materials

Contact Material: Brass

Insulation Material: Polyester UL94V-0

PBT

Contact plating: 30U' Gold

All materials must be GP materials

NUMBER OF POSITION	Dimensions	
	A	B
10	20.32	12.70
14	25.40	17.78
16	27.94	20.32
20	33.02	25.40
26	40.64	33.02
30	45.72	38.10
34	50.80	43.18
40	58.42	50.80
50	71.12	63.50
60	83.82	76.20
64	88.90	81.28

CnC Tech, LLC

Industrial Cable and Connector Technology

DESIGN *lumayl*

DATE 2011. 12. 05

CHECKED

PART NO.

REV

A

UNIT

mm

3020-XX-0200-02

SIZE

A4



UNLESS OTHERWISE SPECIFIED TOLERANCE

ANG ±5°

0 ±0.3

.0 ±0.15

.00 ±0.10