

THA-102 Pulls




Characteristic

With feet or without feet are available.

Application

Measuring instruments /
Telecommunication devices



※ Tapped depth of THA-102-2:
Approx. 10mm.

Parts List

The figure shows the pull with feet.

Model No.	Type	Allowable Vertical Load kN(kgf)	Net Weight(g)	Code No.
THA-102-1	With Feet	785 (80)	63	3503
THA-102-2	Without Feet	785 (80)	57	3504

No.	Part Name	Material	Finish	Quantity
1	Pull Without Feet	ZDC	Cr	1
2	Headless Screw	S15C	Uc	2

THA-101 Pulls




Characteristic

With feet or without feet are available.

Application

Measuring instruments /
Telecommunication devices



※ Tapped depth of THA-101-2:
Approx. 10mm.

Parts List

The figure shows the pull with feet

Model No.	Type	Allowable Vertical Load kN(kgf)	Net Weight(g)	Code No.
THA-101-1	With Feet	981 (100)	78.5	3500
THA-101-2	Without Feet	981 (100)	70.5	3501

No.	Part Name	Material	Finish	Quantity
1	U-Shaped Pull (Large) Without Feet	ZDC	Cr	1
2	Headless Screw	S15C	Uc	2

THA-112 Pulls




Characteristic

With feet or without feet are available.

Application

Measuring instruments /
Telecommunication devices



※ Tapped depth of THA-112-2:
Approx. 8mm.

Parts List

The figure shows the pull with feet.

Model No.	Type	Allowable Vertical Load kN(kgf)	Net Weight(g)	Code No.
THA-112-1	With Feet	1.37 (140)	57.5	3522
THA-112-2	Without Feet	1.18 (120)	50.0	3523

No.	Part Name	Material	Finish	Quantity
1	U-Shaped Pull (Small) Without Feet	ZDC	Cr	1
2	Headless Screw	SUM	Uc	2