



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	PRODUCT WORKS WITH PANDUIT PART NUMBERS:	APPLICATION SURFACE:	WEIGHT lbs / 10 (g) / pcs.
JMTRB38-3-	JMJH2 JMOD CABLE SUPPORT	1/4" or 3/8" THREADED ROD	5.20 (2360)



NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER DESIGNATION, PACKAGE SIZE OPTIONS AND COLOR.
2. TWO NUTS APPROPRIATE FOR THE THREADED ROD USED ARE REQUIRED TO COMPLETE A RIGID INSTALLATION.
3. ASSEMBLY COMPONENT MATERIALS:
 - A. PRE-GLAVANIZED STEEL (JMCMB25-1)
 - B. ZINC PLATED STEEL (RIVET)
 - C. SPRING STEEL (THREADED ROD BRACKET)
4. RATED STATIC LOAD: 180 lbs. (81.65kg)
5. JMTRB38-3 WILL ACCEPT A MAXIMUM OF SIX JMJH2 J HOOK PRODUCTS.



DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G02672DR_PB_JMTRB383_00

PANDUIT

CORP. TINLEY PARK, ILLINOIS

JMOD DROP WIRE
BRACKET ASSEMBLY
(JMTRB38-3-)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JAD

MAT'L:

SCALE NONE

DATE 3/17/03

SEE NOTE 3

DRAWING NO.

GB2672DR

DWG
SIZE
A

R	3/7/03	JAD		INITIAL RELEASE	GB2722DR	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	