




FK30M

Long stem heavy duty T-handle penetration probe



Copyright © 2007 Test Products International, Inc.

Application

Heavy duty penetration into
semi-solids and liquids straight
shaft resists bending

Range°F°C

-58° to 500°F
-50° to 250°C

Probe tip

20

Dimensions

Stem Length: 24" (609.6mm)
Diameter: 3/8" (9.52mm)
Lead Length: 39.4" (1M)

Insulation Material

Polyurethane