


DIP

RTE Series Low Profile Rotary DIP Switches

SWITCHES WITH STANDARD OPTIONS


PC Mount-Terminal Option N

PART NUMBER WITHOUT ESD PIN	WITH ESD PIN	NO. POS.	FUNCTION	QTY PER TUBE
RTE0200N04	RTE0210N04	2	SPDT	65
RTE0300N04	RTE0310N04	3	SP3T	65
RTE0400N04	RTE0410N04	4	SP4T	65
RTE1000N14	RTE1010N14	10	BCD	65
RTE1600N44	RTE1610N44	10	HEXADECIMAL	65




Right Angle Mount-Terminal Option V

PART NUMBER	NO. POS.	FUNCTION	QUANTITY
RTE0400V04	4	SP4T	150 per box
RTE1000V14	10	BCD	150 per box
RTE1600V44	16	HEXADECIMAL	150 per box



Surface Mount-Terminal Option G

PART NUMBER	NO. POS.	FUNCTION	QUANTITY PER REEL
RTE0200G04	02	SPDT	1250
RTE0300G04	03	SPDT	1250
RTE0400G04	04	SP4T	1250
RTE1000G14	10	BCD	1250
RTE1600G44	16	HEXADECIMAL	1250




Dimensions are shown: Inch (mm)
Specifications and dimensions subject to change


RTE Series Low Profile Rotary DIP Switches

NUMBER OF POSITIONS


RTE02* 2 POSITION




RTE03 3 POSITION




RTE04 4 POSITION



RTE10 10 POSITION




RTE16 16 POSITION




ESD PROTECTION

0 WITHOUT




1 WITH




ACTUATOR


0 FLUSH, SCREWDRIVER SLOT



1 EXTENDED SHAFT
(not available in surface mount)



2 SHAFT FOR BUTTON



Third Angle
Projection


RTE Series

Low Profile Rotary DIP Switches


TERMINATIONS




N THRU-HOLE




RTE10, RTE 04 or RTE16
with ground terminal




RTE10, RTE 04 or RTE16
without ground terminal




RTE02 with
ground terminal




RTE02 without
ground terminal



RTE03 with
ground terminal




RTE03 without
ground terminal




Ø in PC Board for screw driver operation must be 3.5 mm


R REVERSE, THRU-HOLE




RTE10, RTE 04 or RTE16
with ground terminal




RTE10, RTE 04 or RTE16
without ground terminal




RTE02 with
ground terminal




RTE02 without
ground terminal



RTE03 with
ground terminal




RTE03 without
ground terminal



Reverse version = R
operation from
bottom side

Ø 3,5 Min.
Ø (0.138 min)

Ø in PC Board for screw driver operation must be 3.5 mm



Third Angle
Projection


Dimensions are shown: Inch (mm)
Specifications and dimensions subject to change

RTE Series Low Profile Rotary DIP Switches


TERMINATIONS



V RIGHT ANGLE, THRU-HOLE





G SURFACE MOUNT



PCB layout seen component side

M OPTION



Dimensions are shown: Inch (mm)
Specifications and dimensions subject to change

DIP —

2 BCD COMPLEMENT CODE

POS.	1	2	3	4
C	●	●	●	●
1	●			
2		●		
3			●	
4				●

[illegible][illegible]

Other codes available by request.

3 GREY CODE (for RTE10 only)

[illegible]

4 HEXADECIMAL CODE

POS.	0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
C	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
1		●		●		●		●		●		●		●		●
2			●	●			●	●			●	●			●	●
4					●	●	●	●					●	●	●	●
8									●	●	●	●	●	●	●	●

7 GREY CODE (for RTE04 and RTE16 only)

[illegible]

OPTION CODE	RoHS COMPLIANT *	RoHS COMPATIBLE *	CONTACT MATERIAL	TERMINAL PLATING	RATINGS		
*4	YES	YES **	GOLD	MATTE TIN	100 mA max.	10μ A min.	30 V DC max.
*5	YES	YES **	SILVER	MATTE TIN	100 mA max.	1 mA min.	50 V DC max.





* Note: See Technical Data section of this catalog for RoHS compliant and compatible definitions and specifications.

* When selecting contact material option 4 and 5 with RTE02, RTE03 and/or "V" terminations, these combinations are RoHS compliant but not currently compatible (i.e. they do not sustain the high temperatures of the leadfree soldering process). All other options and terminations are RoHS compatible. Please contact customer service for RoHS compatible versions of the RTE02 and RTE03.

BUTTONS AVAILABLE

Buttons are ordered separately, shipped in bulk.


Part Number	Color
BTN RTE 40	Red
BTN RTE 50	Green
BTN RTE 90	Black




Dimensions are shown: Inch (mm)
Specifications and dimensions subject to change

TAPE AND REEL


Tape and reel for RTExx02Gxx
750 pieces per reel.



Tape and reel for RTExx00Gxx
1,250 pieces per reel.



Note: Dimensions in: $\frac{\text{inches}}{(\text{mm})}$



Dimensions are shown: Inch (mm)
Specifications and dimensions subject to change