




AMERICAN
ELECTRICAL, INC.

INDUSTRIAL ELECTRICAL ACCESSORIES

Insulated Wire Ferrules
DIN 46228 Part 4



		DIN		T		W		Pieces per bag	Dimensions (mm)						Recommended Crimping Tool
Size mm ²	AWG	Part Number	Color Code DIN	Part Number	Color Code T	Part Number	Color Code W		L-1	L-2	D-1	S-1	D-2	S-2	
0.14	26-28	1161014 1181014	GREY	1163014 1183014	BROWN	1162014 1182014	GREY	500 500	10.5 12.5	6 8	0.8 0.8	0.25 0.25	2 2	0.25 0.25	SQ28-10
0.25	24-26	11610025 11810025	YELLOW	11630025 11830025	VIOLET	11620025 11820025	BLUE	500 500	10.5 12.5	6 8	0.8 0.8	0.25 0.25	2 2	0.25 0.25	TRAP24-10 or SQ28-10
0.34	22-24	1161034 1181034	TURQ	1163034 1183034	PINK	1162034 1182034	TURQ	500 500	10.5 12.5	6 8	0.8 0.8	0.25 0.25	2 2	0.25 0.25	
0.5	20-24	1161050 1181050 11101050	WHITE	1163050 1183050 11103050	WHITE	1162050 1182050 11102050	ORANGE	500 500 500	11.5 13.5 15.5	6 8 10	1.1 1.1 1.1	0.15 0.15 0.15	2.5 2.5 2.5	0.25 0.25 0.25	
0.75	20-22	1161075 1181075 11101075 11121075	GREY	1163075 1183075 11103075 11123075	BLUE	1162075 1182075 11102075 11122075	WHITE	500 500 500 500	12 14 16 18	6 8 10 12	1.3 1.3 1.3 1.3	0.15 0.15 0.15 0.15	2.8 2.8 2.8 2.8	0.25 0.25 0.25 0.25	
1	18	1161010 1181010 11101010 11121010	RED	1163010 1183010 11103010 11123010	RED	1162010 1182010 11102010 11122010	YELLOW	500 500 500 500	12.5 14.5 16.5 18.5	6 8 10 12	1.5 1.5 1.5 1.5	0.15 0.15 0.15 0.15	3 3 3 3	0.3 0.3 0.3 0.3	
1.5	16	1161015 1181015 11101015 11121015 11181015	BLACK	1163015 1183015 11103015 11123015 11183015	BLACK	1162015 1182015 11102015 11122015 11182015	RED	500 500 500 500 500	12.5 14.5 16.5 18.5 24.5	6 8 10 12 18	1.8 1.8 1.8 1.8 1.8	0.15 0.15 0.15 0.15 0.15	3.4 3.4 3.4 3.4 3.4	0.3 0.3 0.3 0.3 0.3	
2.08	14	1181208	YELLOW	1183208	YELLOW	1182208	YELLOW	500	14.5	8	2.05	0.15	3.6	0.3	
2.5	14	1181025 11121025 11181025	BLUE	1183025 11123025 11183025	GREY	1182025 11122025 11182025	BLUE	500 500 500	15 19 25	8 12 18	2.3 2.3 2.3	0.15 0.15 0.15	4.2 4.2 4.2	0.3 0.3 0.3	
4	12	11101040 11121040 11181040	GREY	11103040 11123040 11183040	ORANGE	11102040 11122040 11182040	GREY	500 500 100	17.5 20 26	10 12 18	2.9 2.9 2.9	0.2 0.2 0.2	4.8 4.8 4.8	0.3 0.3 0.3	
6	10	11121060 11181060	YELLOW	11123060 11183060	GREEN	11122060 11182060	BLACK	100 100	20 25	12 18	3.6 3.6	0.2 0.2	6.2 6.2	0.3 0.3	
10	8	11121100 11181100	RED	11123100 11183100	BROWN	11122100 11182100	IVORY	100 100 100	21 27 27	12 18 18	4.6 4.6 4.6	0.2 0.2 0.2	7.5 7.5 7.5	0.3 0.3 0.3	TRAP8-1 or TRAP 8-4
16	6	11121160 11181160	BLUE	11123160 11183160	WHITE	11122160 11182160	GREEN	100 100	23 29	12 18	6 6	0.2 0.2	8.8 8.8	0.4 0.4	
25	4	11161250 11181250 11221250	YELLOW	11163250 11183250 11253250	BLACK	11162250 11182250 11222250	BROWN	50 50 50	29 31 35	16 18 22	7.5 7.5 7.5	0.2 0.2 0.2	11 11 11	0.5 0.5 0.5	
35	2	11161350 11181350	RED	11163350 11183350	RED	11162350 11182350	BEIGE	50 50	30 32	16 18	8.5 8.5	0.2 0.2	12.5 12.5	0.5 0.5	TRAP8-1

		11251350			11253350			11252350			50	39	25	8.5	0.2	12.5	0.5	VICE70150
50	1	11201500		BLUE	11203500		BLUE	11202500		OLIVE	50	36	20	10.5	0.35	15	0.6	
		11251500			11253500			11252500			25	41	25	10.5	0.35	15	0.6	
70	1 / 0	11201700		YELLOW	11203700		YELLOW	11202700		YELLOW	25	37	20	12.7	0.35	16	0.6	
70	2 / 0	11271700		YELLOW	11273700		YELLOW	11272700		YELLOW	25	43	27	12.7	0.4	16	0.6	VICE70150
95	3 / 0	11251950		RED	11253950		RED	11252950		RED	25	44	25	14.7	0.35	18	0.6	
120	4 / 0	112711200		BLUE	112731200		BLUE	112721200		BLUE	25	48	27	16.7	0.45	21	0.7	
	300																	VICE70150
150	MCM	113211500		YELLOW	113231500		YELLOW	113221500		YELLOW	25	58	32	19.5	0.5	23	1	

[Purchase Here!](#)