

1075 HardBack Case



Interior dimensions:
28.2 x 20.1 x 4.1 cm (11" x 8" x 2")

Designed to protect various electronics including external hard drives

Watertight Gasket - Tight seal created when case is shut

The easy open latch remains shut under pressure or after impact

Automatic Purge Valve - Keeps water and dust out while balancing air pressure

Pick N Pluck™ with convoluted lid foam

Removable shoulder strap included

Legendary Guarantee of Excellence

Visit our

Watertight, crushproof, and dust proof



Black

1075 HardBack Case SPECIFICATIONS

Exterior Dimensions (L x W x D)		Interior Dimensions (L x W x D)			
31.4 x 24.8 x 5.4 cm (12" x 10" x 2")		28.2 x 20.1 x 4.1 cm (11" x 8" x 2")			
Lid Depth		Bottom Depth			
2.1 cm (0.81")		4.1 cm 1.63")			
Lid Depth		Total Depth			
2.1 cm (0.81")		4.1 cm 1.63")			
Weight w/Foam		Weight w/o Foam			
0.7 kg. (1.54 lbs.)		0.64kg (1.41 lbs.)			
Buoyancy Max.					
0 kg (lbs.)					
Range Temperature					
-23 / 49° C (-10 / 120° F)					

Materials

Body	Latch	Lid O-Ring	Pins
ABS	ABS	EPDMStainless Steel	
Foam	Purge Body	Purge Vent	Purge O-Ring
	Polycarbonate	PTFE	70 Shore Nitrile

Configuration

Cat. #	Description
1075	1075 HardBack Case

1075 HardBack Case Accessories

No accessories are currently available for this product