

# FLEX STACK

# MICRO BOARD STACKER

(1.27 mm) .050" PITCH • FW SERIES

4  
Gbps

## FW

**Board Mates:**

CLP, FLE

**Cable Mates:**

FFSD

## SPECIFICATIONS

**Insulator Material:**

Black Liquid Crystal Polymer

**Terminal Material:**

Phosphor Bronze

**Plating:**

Sn or Au over 50 μ" (1.27 μm) Ni

**Operating Temp Range:**

-55 °C to +125 °C

## PROCESSING

**Lead-Free Solderable:**

Yes

**SMT Lead Coplanarity:**

(0.10 mm) .004" max (02-30)

(0.15 mm) .006" max (31-50)\*

\*(.004" stencil solution may be available; contact ipg@samtec.com)

## MATED HEIGHT

| FW<br>LEAD STYLE     | CLP<br>LEAD STYLE | MATED<br>HEIGHT*   |
|----------------------|-------------------|--------------------|
| FW-XX-03-X-X-233-065 | -02               | (8.13 mm)<br>.320" |
| FW-XX-03-X-X-303-065 |                   | (9.91 mm)<br>.390" |

\*Processing conditions will affect mated height.

## ALSO AVAILABLE

Contact Samtec

Smaller stack heights


## Notes:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.


This Series is non-standard, non-returnable.

| FW | NO. OF PINS PER ROW | LEAD STYLE                    | PLATING OPTION                                                                                                                                                               | D | STACKER HEIGHT                                                                      | POST HEIGHT                                                                                                      | OPTION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|----|---------------------|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|    | 02 thru 50          | Specify LEAD STYLE from chart | -F<br>= Gold flash on post, Matte Tin on tail<br><br>-L<br>= 10 μ" (0.25 μm) Gold on post, Matte Tin on tail<br><br>-G<br>= 10 μ" (0.25 μm) Gold on post, Gold flash on tail |   | -“XXX”<br>= Stacker Height (in inches)<br><br>Example:<br>-250<br>= (6.35 mm) .250" | -“XXX”<br>= Post Height (in inches)<br><br>(1.65 mm) .065" minimum<br><br>Example:<br>-.065<br>= (1.65 mm) .065" | -ES<br>= End Shroud (-075 post height only. Mate only with CLP) (5.46 mm) .215" to (15.49 mm) .610" stacker height only 9 pins/row min.<br><br>-EP<br>= End Shroud with Guide Post (-075 post height only. Mate only with CLP) (5.46 mm) .215" to (15.49 mm) .610" stacker height only 9 pins/row min.<br><br>-A<br>= Alignment Pin (3 positions min.) (5.46 mm) .215" to (15.75 mm) .620" stacker height only (SMT only)<br><br>-P<br>= Pick & Place Pad (5 positions min.) (SMT only)<br><br>-TR<br>= Tape & Reel (Max overall height = Post+Stacker Height+Pad+Alignment Pin = (17.78) .700" (SMT only)<br><br>-FR<br>= Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (SMT only) |



| LEAD STYLE | STACKER HEIGHT                 | STACKER + POST                  |
|------------|--------------------------------|---------------------------------|
| -03        | (5.46) to (8.51)<br>.215 .335  | (7.11) to (10.16)<br>.280 .400  |
| -05        | (6.30) to (15.49)<br>.248 .610 | (10.29) to (17.15)<br>.405 .675 |



SURFACE MOUNT



THROUGH-HOLE



POST HEIGHT  
(1.65)  
.065 MIN

