



TYPE A - 4+4 TO 26+26 WAYS INCLUSIVE:



TYPE B - 2+2, 3+3 AND 27+27 TO 36+36 WAYS:



GENERAL:

- NOTES:
- 2+2 & 3+3 WAY: LENGTH = 2.54 ± No. OF PITCHES PER ROW + 2.48 MAX (MOULDED).
 - 27+27 TO 36+36 WAYS: LENGTH = 2.54 ± No. OF PITCHES PER ROW + 3.30 MAX (MACHINED).
 - RECOMMENDED PCB HOLE = ø0.85 MIN.
 - MAXIMUM PIN LENGTH = 7.0mm.
 - MATERIAL:
MOULDING = GLASS-FILLED POLYESTER UL94V-0, BLACK.
CONTACTS = PHOSPHOR BRONZE.
 - FINISH:
06 = 90/10 TINLEAD.
22 = GOLD ON CONTACT FACE OVER NICKEL,
90/10 TINLEAD ON TAILS.

ORDER CODE:

No. OF WAYS PER ROW
02 TO 36 (2+2 TO 36+36)

FINISH
06 = TINLEAD
22 = SELECTIVE GOLD

M20-983X

CUSTOMER
INFORMATION
SHEET

14	05.08.95	3475
13	11.05.95	3352
12	17.11.95	3104
11	25.03.95	3049
3	10.02.94	2536
2	17.03.93	2223
1	13.09.89	----

ISS.	DATE	C/N
APPROVED:		
CHECKED:		
DRAWN: W. BOURNE		
CUSTOMER REF.		
ASSEMBLY DRO:		

HARWIN

HARWIN INC
U.S.A.

TEL: (812) 285 0055
FAX: (812) 285 0056

HARWIN PLC
U.K.

TEL: 01705 370451
FAX: 01705 324010

HARWIN PTE
SINGAPORE

TEL: 65 7794903
FAX: 65 7793868

HARWIN CONNECTORS
KOREA

TEL: 822 521 0747
FAX: 822 521 0749

TOLERANCE

X. = ±1mm

X.X = ±0.25mm

X.XXX = ±0.10mm

X.XXX = ±0.05mm

ANGLES = ±1°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE TABLE

AREA: mm²

TITLE:

2.54mm DIL VER
SOCKET (NARR)

DRAWING NUMBER:

M20-983XXXX

SH1
2
OF
2