



XTRAFLEX Liquidtight Conduit Tubing & Fittings

T&B Catalog Number:

UPC Number: LTC200
 Status: 78621078959
 Description: Active

2 in. black non-metallic Type B industrial grade liquidtight conduit.

Features

Fast installation, even in tight or cramped spaces.
 Smooth inner diameter allows easy wire pulling.
 Smooth outer jacket uses material approved for out-
 door use, is sunlight resistant and oil resistant.
 Lightweight and liquidtight.

Application

Machine tools, motor hookups, food processing
 equipment, extensions from wire ways, and sensor
 and micro switch wiring found in control consoles.
 UL Listed for direct burial

General

Material: PVC
 Color: Black
 Working Temperatures: -18 C to +105 C

Dimension Information

Size (inches): 2
 I.D. - Minimum (inches): 2.02
 I.D. - Maximum (inches): 2.045
 O.D. - Minimum (inches): 2.34
 O.D. - Maximum (inches): 2.375

Packaging

T&B Order Multiple: 50
 Package in Units: 50
 T&B Sold in UOM: Feet
 T&B Weight Per UOM: 74.3 lbs. per 100

Application Support

Guide to Nonmetallic Conduit Applications Available on Website
 XTRAFLEX System Specifications Available on Website

Certifications

RoHS Compliance: Yes

Certifications



File Nbr:
 E 95745

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com