


Global RF Solutions

☐ Part Number ☒ Text
☐ RoHS Compliant

products site tools rf made simple distributors about us newsletter contact us login
Toll Free: (800) 627-7100
Inside CT: (203) 743-9272

[Amphenol Worldwide](#)
[Amphenol RF Employment](#)
[Engineering Focus](#)
[Quality Focus](#)
[Weather and Directions](#)
[Locate A Distributor](#)
[Check Distributor Inventory](#)
[Frequency Range Chart](#)
[Glossary](#)
[Technical Questions](#)
[VSWR Calculator](#)
[VSWR Chart](#)

[Product Overview](#)
[Product Search](#)
[Cross Reference](#)
[QPL Products](#)
[Markets Served](#)
[Product Literature](#)
[Newsletter](#)
[Customer Extranet](#)
[Salesperson Extranet](#)
[Vendor Extranet](#)
[Employee Extranet](#)
[Internal Employee Extranet](#)
[Amphenol RF Manufacturers Rep.](#)


product details

Product Search

[1.0/2.3](#)
[1.6/5.6](#)
[AFI](#)
[AMC](#)
[BNC / RP-BNC](#)
[C](#)
[FAKRA SMB](#)
[FME](#)
[HD BNC](#)
[HN](#)
[MCX](#)
[Mini BNC](#)
[Mini UHF](#)
[Mini 75 \$\Omega\$ SMB](#)
[MMCX](#)
[Precision \(APC\)](#)
[QMA](#)
[SC](#)
[SMA / RP-SMA](#)
[SMB](#)
[SMC](#)
[SMP](#)
[SSMB](#)
[TNC / RP-TNC](#)
[Triax](#)
[True 75 \$\Omega\$ BNC](#)
[Twin BNC](#)
[Twinax](#)
[Type F](#)
[Type G](#)
[Type N](#)
[UHF](#)
[Reverse Polarity](#)

[Adapters](#)
[Tools](#)
[Accessories](#)

[Product Search](#)
 src="/images/dottedline.gif"
 >
[Inventory Search](#)



Please note: Images are for reference only

Amphenol Part Number: 031-5557-RFX
Product Series: [BNC](#)
Product Type: [Connectors](#) » [Cable](#)
Application: [Crimp](#)
Body Plating: [Nickel](#)
Body Termination: [Crimp](#)
Cable Group: [C](#)
Cable Type: [89907](#), [B7806A](#), [RG-141](#), [RG-58](#), [RG-58C](#)
Connector Body Style: [Straight](#)
Contact Plating: [Gold](#)
Contact Termination: [Press Fit](#)
Gender: [Plug](#)
Grade: [Commercial](#)
Impedance: [50 Ohm](#)
RoHS Certificate: [Yes](#)
IGS File Download: [IGS File](#)
More Information: [Assembly Instructions](#)
[Customer Drawing](#)
[Distributor Inventory](#)

