

Part Number: AOM-4540P-NF-R



Features

Omnidirectional
Super clarity, distortion-free response
Pin type mounting
This part is RoHS 2002/95/EC Compliant

Electrical Specifications

Directivity

Omnidirectional

Impedance

2.2 kOhm

Operating Voltage

1.5 Vdc

Package Size

9.7 x 4.5 mm


Sensitivity

-40 +/- 3 dB


Environmentally friendly

Mechanical

Dimensions are in millimeters, tolerance is ± 0.5 unless otherwise specified.



Performance



For application notes and detail drawing specifications, please consult www.projectsunlimited.com.

Specifications subject to change without notice.

© 2006, Projects Unlimited Inc., All Rights Reserved.