

Between Series Adaptor 33_SMA-N-50-1/1--_U

Description

Adaptor plug/jack
SMA plug (male) / N jack (female)

Interface standards

Series SMA - IEC 60169-15_MIL-STD-348A/310_CECC 22110

Series N - IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz
VSWR	DC - 12.4 GHz ≤ 1.05 + 0.015 f (GHz)

Mechanical Data

Number of matings	500
Weight	0.0214 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS)	compliant

Material Data

Interface - SMA plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Coupling nut	Bronze	Gold Plating (without Nickel underplating)
Gasket	VMQ (Silicone rubber)	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00014248
-------------------	--------------

Ordering Information

Single package	33_SMA-N-50-1/1--_UE
----------------	----------------------