

SS-132-G-2

ESD-115-G-05

(2,54 mm) .100"

SS, SD, ESD, ESS, HSS SERIES

PRECISION MACHINED SOCKET STRIPS

Mates with:
TS, TD, HTS, BBS,
BBD, BBL, BDL, BHS

SPECIFICATIONS

For complete specifications see www.samtec.com?SS, www.samtec.com?ESS, www.samtec.com?SD, www.samtec.com?ESD or www.samtec.com?HSS

Insulator Material:
SS, SD, ESS, ESD= Black G.F. Polyester
HSS= Black Liquid Crystal Polymer
Contact:
BeCu

Shell:
Brass except Style 5A
Phosphor Bronze

Plating:
Au over 50µ" (1,27 µm) Ni or
Sn over 50µ" (1,27 µm) Ni
Operating Temp Range:
-55°C to +125°C

Contact Resistance:
10 mΩ

Lead Size Range:
(0,38 mm to 0,56 mm)
.015" to .022" DIA
and most IC leads

Insertion Force:
(Single contact only)
Standard=

9 oz (2,50 N) avg.,
16 oz (4,45 N) max

Low Insertion Force=

2.5 oz (0,70 N) avg.,
5.5 oz (1,53 N) max

Withdrawal Force:
(Single contact only)
Standard=

2.5 oz (0,70 N) avg.,
1.5 oz (0,42 N) min

Low Insertion Force=

2.0 oz (0,56 N) avg.,
0.35 oz (0,10 N) min

Insertion Depth:
(-05, -1X & -21X, -5A)

(3,18 mm) .125" to
(3,99 mm) .157"

Insertion Depth:
(-2, -22, -38)

(2,41 mm) .095" to
(3,68 mm) .145"

RoHS Compliant:

Yes
Lead-Free Solderable:
Wave only

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

TYPE STRIP	1	NO. PINS PER ROW	PLATING OPTION	LEAD STYLE	OPTION	OTHER OPTION
------------	---	------------------	----------------	------------	--------	--------------

01 thru 32

= SS, ESS Series

01 thru 36

= HSS, SD & ESD Series

SS

= Standard Single Row Socket


HSS

= High Temp Single Row Socket

ESS

= Elevated Single Row Socket

Styles -5A & -05 socket heads not countersunk.




SD

= Standard Double Row Socket

ESD

= Elevated Double Row Socket

Style -5A not available.
Styles -5A & -05 socket heads not countersunk.



LIF= Low Insertion Force

Note:
Some lengths, styles and options are non-standard, non-returnable.

-S

= 10µ" (0,25 µm) Gold contact,
Tin shell
(Styles 2 & 22 only)

-T

= 30µ" (0,76 µm) Gold contact,
Tin shell

-G


= 30µ" (0,76 µm) Gold contact,
10µ" (0,25 µm) Gold shell

-TT

= Tin contact and shell
(Styles 1, 2, 4, and 05 except LIF N/A)


-L = Locking Socket

Add -L suffix for locking lead socket in end positions. Requires Style -2 or -22 and .035" ± .003 DIA board hole.



Requires -T Plating Option

-N = Non Flush




N/A Style -5A

ALSO AVAILABLE (MOQ Required)

- Locking lead option on ESS and ESD series
- Contact Samtec.

-1A, -1B or -1C


For LIF specify -21A, -21B or -21C
(SS, HSS, SD)



LEAD STYLE	Y
-1A or -21A	(9,14) .360
-1B or -21B	(12,95) .510
-1C or -21C	(6,60) .260

-2, -22*, -5A,
or -38*


*For LIF specify -22 or -38 (SS, HSS, SD)



Locking lead available. See OPTION.

-03, -04, -05

For LIF specify -23
(ESS, ESD)



LEAD STYLE	A	B	C
05	(17,86) .703	(13,46) .530	(4,39) .173
03 or 23	(11,51) .453	(8,38) .330	(3,12) .123
04	(14,05) .553	(10,92) .430	(3,12) .123

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685