



1	2	3	4	5	6
---	---	---	---	---	---



Bestell-Nummer / Part No.		D	Leiterquerschnitt wire gauge		Abisolierlänge der Litze stripping length
versilbert silver plated	vergoldet gold plated		mm²	AWG	
09 15 000 6104	09 15 000 6124	0,90	0,14-0,37	26-22	8
09 15 000 6103	09 15 000 6123	1,10	0,5	20	
09 15 000 6105	09 15 000 6125	1,30	0,75	18	
09 15 000 6102	09 15 000 6122	1,45	1	18	
09 15 000 6101	09 15 000 6121	1,75	1,5	16	
09 15 000 6106	09 15 000 6126	2,25	2,5	14	6

		 ALL Dimensions in mm Original Size DIN A 4		Techn. Character.			Nicht tolerierte Masse/ Free size tolerances Han D / R15 Stiftkontakt Crimpkontakt gedreht 10A <i>crimpcontact turned 10A</i>		
					Dat.	Name			Massstab/ Scale 2:1
				Detail.	22.03.99	Kö			
				Insp.		SDT			
				Stand.					
		412766	07.03.07	Ho	HARTING Electric GmbH & Co. KG D-32339 Espelkamp		TB 09 15 000 61..		Blatt/ page /
		25592							
Bestell-Nr/Part No		Mod.	Dat.	Name			Sub. TB 09 15 000 6... v. 22.02.93		