





- 1 PARTS COMPLY WITH AMP SOLDERABILITY SPECIFICATION 109-11-5.
- 2 TOLERANCE NON-CUMULATIVE.
- 3 0.00076 [.000030] GOLD OVER 0.00127 [.000050] MIN NICKEL WITH MATTE TIN LEAD ON SOLDER TAIL.
- 4 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- 6 0.00076 [.000030] GOLD OVER 0.00127 [.000050] MIN NICKEL WITH MATTE TIN ON SOLDER TAIL.
- 7 SUPERSEDED BY 3-643232-0



PH BRZ GOLD, 6		NYLON UL 94V-0	3-643232-0
PH BRZ GOLD, 3		NYLON UL 94V-0	643232-2
PH BRZ PRE-TIN		NYLON UL 94V-0	643232-1
CONTACT		HOUSING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 21APR2005	TE Connectivity	
		CHK S. RIDGILL 21APR2005		
DIMENSIONS: mm [INCHES]		APVD S. RIDGILL 21APR2005	NAME	
		PRODUCT SPEC	SOCKET HEADER ASSEMBLY, RIGHT ANGLE MOUNT, 5 POSITION, UNIVERSAL MATE-N-LOK(TM)	
		APPLICATION SPEC		
MATERIAL SEE TABLE		WEIGHT -	SIZE A1	RESTRICTED TO -
			CAGE CODE 00779	
			DRAWING NO. 643232	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV D1