


Rubber Grommet NG-79-Type



Model No.	Material	Hardness	Color
NG-79	EPDM	55°±5°	Black



Characteristic

Installation can be made with a single touch and it is effective on preventing wire disconnection.

Application

Computers / Measuring instruments /
Telecommunication devices /
Electric appliances, etc.

Model No.	A	B	C	D	E	F	Net Weight(g)	Code No.
NG-79-1	9	6	3.5	3.7	1.2	R0.6	0.2	5202
NG-79-A	11	8	5	4.5	1.5		0.4	5203
NG-79-A-1				4	1		0.3	5204
NG-79-A-2				5	2		0.3	5205
NG-79-B				6	3		0.4	5206
NG-79-C	13	10	7	4.5	1.5	R0.6	0.6	5207
NG-79-D				6	3		0.6	5208
NG-79-E	15	12	9	4.5	1.5		0.6	5209
NG-79-F				6	3		0.6	5210
NG-79-G	19	15	11	5.5	1.5	R1	1.2	5211
NG-79-H				7	3		1.4	5212
NG-79-J	21	17	13	5.5	1.5		1.5	5213
NG-79-K				7	3		1.5	5214
NG-79-L	23	19	15	5.5	1.5		1.6	5215
NG-79-M				7	3		1.7	5216
NG-79-N	30	25	20	6.5	1.5	R1.2	3.0	5217
NG-79-O				8	3		3.2	5218
NG-79-P	35	30	25	6.5	1.5		3.5	5219
NG-79-Q				8	3		4.0	5220
NG-79-R	42	36	30	7.5	1.5		6.1	5221
NG-79-S				9	3		6.9	5222

Rubber Grommet B-Type




Characteristic

Installation can be made with a single touch and it is effective on preventing wire disconnection.

Application

Measuring instruments / Telecommunication devices /
Electric appliances, etc.

Model No.	Material	Hardness	Color
B	EPDM	50°±5°	Black



Model No.	A	B	C	D	E	F	Net Weight(g)	Code No.
B-6-1	18	12	6	7	1	R3	1.6	5231
B-6-2				8	2		1.6	5232
B-8-1	20	14	8	7	1		2.2	5233
B-8-2				8	2		2.2	5234
B-10-1	22	16	10		1		2.5	5235
B-10-2				9	2		2.5	5236
B-12-1	26	19	12	10	1	R4	4.3	5237
B-12-2				11	2		4.4	5238
B-14-1	29	22	14	10	1		5.2	5239
B-14-2				11	2		5.5	5240
B-16-1	32	25	16	10	1		6.5	5241
B-16-2				11	2		7.1	5242
B-19-1	35	28	19	12	1	R5	8.5	5243
B-19-2				13	2		9.2	5244
B-22-1	40	32	22	12	1		10.6	5245
B-22-2				13	2		10.9	5246
B-25-1	44	36	25	14	1	R6	14.8	5247
B-25-2				15	2		15.3	5248
B-28-1	48	40	28	14	1		17.5	5249
B-28-2				15	2		18.1	5250
B-32-1	52	44	32	18	1	R8	23.3	5251
B-32-2				19	2		27.9	5252
B-36-1	56	48	36	18	1		26.3	5253
B-36-2				19	2		27.1	5254
B-45-1.5	75	55	45	15.5	1.5	R7	49.9	5255
B-45-3				16.5	3		51.1	5256