




Cable Ties Polyamide 6.6 standard

• T-Series in PA66 coloured

Material Data

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40 °C to +85 °C Continuous, (+105 °C for 500 h)
Flammability	UL94 V2



Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Material	Colour	Application Tool
Polyamide 6.6 Colours								
116-01816	T18R	100	2.5	22.0	80	PA66	Blue (BU)	1–3, 5
111-03008	T30R	150	3.5	35.0	135	PA66	Blue (BU)	1–3, 5
111-04800	T50R	200	4.6	50.0	225	PA66	Blue (BU)	1–10
111-05404	T50L	390	4.6	110	225	PA66	Blue (BU)	1–10
116-08016	T80R	210	4.7	55.0	355	PA66	Blue (BU)	1–10
116-05416	T80L	390	4.7	110	355	PA66	Blue (BU)	1–10
116-01815	T18R	100	2.5	22.0	80	PA66	Green (GN)	1–3, 5
111-03014	T30R	150	3.5	35.0	135	PA66	Green (GN)	1–3, 5
111-05402	T50L	390	4.6	110	225	PA66	Green (GN)	1–10
116-08015	T80R	210	4.7	55.0	355	PA66	Green (GN)	1–10
116-05415	T80L	390	4.7	110	355	PA66	Green (GN)	1–10
111-12001	T120R(E)	387	7.6	100	535	PA66	Green (GN)	6–10
116-01812	T18R	100	2.5	22.0	80	PA66	Red (RD)	1–3, 5
111-03004	T30R	150	3.5	35.0	135	PA66	Red (RD)	1–3, 5
111-04804	T50R	200	4.6	50.0	225	PA66	Red (RD)	1–10
111-05406	T50L	390	4.6	110	225	PA66	Red (RD)	1–10
116-08012	T80R	210	4.7	55.0	355	PA66	Red (RD)	1–10
116-05412	T80L	390	4.7	110	355	PA66	Red (RD)	1–10
111-12002	T120R(E)	387	7.6	100	535	PA66	Red (RD)	6–10
116-01814	T18R	100	2.5	22.0	80	PA66	Yellow (YE)	1–3, 5
111-03006	T30R	150	3.5	35.0	135	PA66	Yellow (YE)	1–3, 5
111-04805	T50R	200	4.6	50.0	225	PA66	Yellow (YE)	1–10
111-05428	T50L	390	4.6	110	225	PA66	Yellow (YE)	1–10
116-08014	T80R	210	4.7	55.0	355	PA66	Yellow (YE)	1–10
116-05414	T80L	390	4.7	110	355	PA66	Yellow (YE)	1–10
116-15014	T150R(H)	365	7.6	100	670	PA66	Yellow (YE)	6–10

All dimensions in mm. Subject to technical changes.



Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.