


THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		, 19 .		LOC CH	DIST 11	P	F	REVISIONS				
© COPYRIGHT 19		BY AMP INCORPORATED.		ALL INTERNATIONAL RIGHTS RESERVED.						ZONE	LTR	DESCRIPTION	DATE	APPD

				A	EC OB20-1083-98	20/AUG/98	RNP
				O	RELEASED FOR PRODUCTION	07/JAN/97	RNP

- 1 MATERIAL- BODY: COPPER ALLOY
BAND: BeCu
- 2 FINISH- BODY AND BAND: 5.08µM[.000200] SILVER
OVER 1.02µM[.000040] NICKEL.
3. WIRE BARREL WILL ACCEPT #10 AWG WIRE.
4. MATES WITH AMP PART NUMBER 194210-1.



				194211-1	
				PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 1 PLC DEC ± 0.5[.02] 2 PLC DEC ± 0.25[.010] ANGLES ± -		DR R N POLK 07/JAN/97		AMP AMP Incorporated Harrisburg, PA 17105-3608	
		CHK - -			
		APPD - -		NAME SOCKET ASSY, 2mm, #10AWG, LUBRICATED UNIVERSAL MATE-N-LOK* II	
		APPD - -			
MATERIAL 1		PRODUCT SPEC -		SIZE B	
FINISH 2		APPLICATION SPEC -		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C-194211	
				SCALE NONE	
				SHEET 1 OF 1	

*MATE-N-LOK IS A TRADEMARK

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

*MATE-N-LOK IS A TRADEMARK

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.