

Housing - HC-HV 6-SMQ-67/O1M25 - 1604933

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON box mounting base HV6, with double locking latch, height 67 mm, with support 1xM25

The illustration shows box mounting bases in the versions with double locking latch and single locking latch, for double locking latch with protective cover



Key commercial data

Packing unit	1 PCE
GTIN	 4 017918 883089
Weight per Piece (excluding packing)	378.77 GRM
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	67 mm
Width	57 mm
Length	117 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HV-HV6
Design	HV6

Housing - HC-HV 6-SMQ-67/O1M25 - 1604933

Technical data

General

Housing type	Box mounting bases
Locking type	With double locking latch
No. of cable exits	1
Cable exit	Lateral
Type of the screw connection	1x M25
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Material lock	High-grade steel
Material grip body interlock	PA-GF

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Housing - HC-HV 6-SMQ-67/O1M25 - 1604933

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 

Drawings

Dimensioned drawing

