




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC., ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED FOR PRODUCTION	11/19/01	MCCORMICK
B	REVISED; BNC PLUG 1 PLACE (ECN 1327)	03/13/03	MCCORMICK
B	ECN 3131: UPDATE DWG FORMAT	12/28/07	D.GRIFFIN
.	.	.	.



NOTES:

MATERIAL:

BODY: BRASS
DIELECTRIC: DELRIN
CENTER PIN: BRASS

FINISH:

BODY: NICKEL PLATED
CENTER PIN: GOLD PLATED

NOTES:

1. CHARACTERISTIC IMPEDANCE: 50 OHMS

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] TOLERANCES TO BE: .X ±.1 [2.5] ANGLES ±2° .XX ±.01 [.25] .XXX ±.005 [.13] OVERALL CABLE LENGTH TOL: ≤ 60 [1524] +3 [76.2] / -0 > 60 [1524] +5% / -0%	APPROVALS	DATE	L-com CONNECTIVITY PRODUCTS		01845		
	DRAWN BY MCCORMICK	11/14/01	CATEGORY		COAXIAL		
	CHECKED BY D.PARHAM	11/14/01	PRODUCT DESCRIPTION		BNC JACK JACK TO PLUG		
	APPROVED BY R.CARRICK	11/12/01	SIZE		FSCM NO. A 43321	DWG. NO. BA840	REV. C
PROJ 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SCALE: NONE		CAD FILE: BA840.SLDDRW		SHEET 1 OF 1