

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

V3-21**CK-A2100****S****V3-21****M**DRAWING
NUMBER**100****100**

ISSUE

100**100**

REVISIONS

A**CO20189****26 MAY 65****B****CO21900****6 JAN 67****C****CO24941****3 DEC 68****D****CO26075****26 AUG 69****E****CO31509****22 JAN 73****F****CO-32395****8 FEB 74****G****CO 56987****SMA 1 OCT 85****H****CO74634****KDR 5 MAY 93**

REPLACES

RELEASE NO.



CHECK

CHECK

CHECK

CHECK

DRAWN



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICSOPERATING FORCE - - - - - 6-14 OZ
RELEASE FORCE - - - - - 4 OZ MIN
RELEASE TRAVEL - - - - - .007 MIN
DIFFERENTIAL TRAVEL - - - - - .006-.016
OVERTRAVEL - - - - - .040 MIN
FREE POSITION - - - - - .625 MAX**ELECTRICAL DATA**CONTACT ARRANGEMENT
S P N C15.1A 1/2HP 125 OR 250 VAC
1/2A 125 VDC, 1/4A 250 VDC
5A 125 VAC "L"

RJ ®

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT .016 LB