





| Catalog Number | A     | B (min) | B (max) | C     | D     | E (min) | E (max) | F | Load Capacity |
|----------------|-------|---------|---------|-------|-------|---------|---------|---|---------------|
| CTS-110        | 10.00 | 9.44    | 11.19   | 9.00  | 8.25  | 0.00    | 1.75    | 3 | 175 LBS.      |
| CTS-112        | 12.00 | 10.81   | 14.56   | 11.00 | 8.25  | 0.00    | 3.75    | 3 | 175 LBS.      |
| CTS-114        | 14.00 | 14.88   | 16.75   | 13.00 | 12.13 | 0.00    | 1.88    | 4 | 175 LBS.      |
| CTS-116        | 16.00 | 15.75   | 19.63   | 15.00 | 12.13 | 0.00    | 3.88    | 4 | 175 LBS.      |
| CTS-118        | 18.00 | 21.63   | 23.63   | 17.00 | 16.00 | 0.00    | 2.00    | 5 | 175 LBS.      |
| CTS-120        | 20.00 | 23.63   | 27.63   | 19.00 | 16.00 | 0.00    | 4.00    | 5 | 175 LBS.      |
| CTS-122        | 22.00 | 26.25   | 31.63   | 21.00 | 16.00 | 0.63    | 6.00    | 5 | 175 LBS.      |
| CTS-124        | 24.00 | 28.25   | 34.63   | 23.00 | 16.00 | 1.63    | 8.00    | 5 | 175 LBS.      |

## TO ORDER, SPECIFY



Stationary Section  
1 - Cabinet Mount  
2 - Strap Mount  
4 - Closed Slot

Length


AR - Automatic Release if desired

For information on mounting slides to Off-Set mounting rail see page 26.

For information on Strap Mount option see page 27.

## Notes


- Right hand shown, left hand opposite.
- Finish: All standard slides are coated with Poxylube™ dry film lubricant.
- All standard slides are designed to lock-out in the extended position and are available with an optional automatic release if lock-out is not desirable.
- Standard hardware packages include all the hardware necessary to mount your Chassis Trak® slides:
  - Rear mounting bracket (B-131) included
  - Bar Nuts (CA8056-06-0020)
  - #10-32 screws and keps nuts
- All sliding members of the standard slide are made from cold rolled steel.
- All Chassis Trak® solid bearing slides are supplied with a quick disconnect feature.
- Optional mounting patterns, slide lengths and extensions are available.
- Pickup tab available for units without a front panel.
- For optional mounting brackets see page 35.



# CTS and CTRS Special Application



## Slide for Off-Set Leg Mounting Rail



| Catalog Number | A     | B (min) | B (max) | C     | D     | E (min) | E (max) | F | Load Capacity |
|----------------|-------|---------|---------|-------|-------|---------|---------|---|---------------|
| CTS-SA-114     | 14.00 | 13.50   | 14.25   | 13.00 | 12.13 | 0.0     | .75     | 4 | 175 LBS.      |
| CTS-SA-116     | 16.00 | 14.06   | 16.81   | 15.00 | 12.13 | 0.0     | 2.75    | 4 | 175 LBS.      |
| CTS-SA-118     | 18.00 | 18.81   | 19.69   | 17.00 | 16.00 | 0.0     | .88     | 5 | 175 LBS.      |
| CTS-SA-120     | 20.00 | 20.81   | 23.69   | 19.00 | 16.00 | 0.0     | 2.88    | 5 | 175 LBS.      |
| CTS-SA-122     | 22.00 | 23.31   | 27.69   | 21.00 | 16.00 | .50     | 4.88    | 5 | 175 LBS.      |
| CTS-SA-124     | 24.00 | 25.31   | 30.69   | 23.00 | 16.00 | 1.50    | 6.88    | 5 | 175 LBS.      |

### TO ORDER, SPECIFY

CTS-SA - [ ] - [ ] - [ ]


Stationary Section

1 - Cabinet Mount

4 - Closed Slot

Length

AR - Automatic Release if desired



### TO ORDER, SPECIFY

CTRS-SA - [ ] - [ ] - [ ]

Stationary Section  
1 - Cabinet Mount  
4 - Closed Slot


Length

AR - Automatic Release if desired

| Catalog Number | A     | B (min) | B (max) | C     | D     | E (min) | E (max) | F | Load Capacity |
|----------------|-------|---------|---------|-------|-------|---------|---------|---|---------------|
| CTRS-SA-114    | 14.00 | 13.50   | 14.25   | 13.00 | 12.13 | 0.0     | .75     | 4 | 175 LBS.      |
| CTRS-SA-116    | 16.00 | 14.06   | 16.81   | 15.00 | 12.13 | 0.0     | 2.75    | 4 | 175 LBS.      |
| CTRS-SA-118    | 18.00 | 18.81   | 19.69   | 17.00 | 16.00 | 0.0     | .88     | 5 | 175 LBS.      |
| CTRS-SA-120    | 20.00 | 20.81   | 23.69   | 19.00 | 16.00 | 0.0     | 2.88    | 5 | 175 LBS.      |
| CTRS-SA-122    | 22.00 | 23.31   | 27.69   | 21.00 | 16.00 | .50     | 4.88    | 5 | 175 LBS.      |
| CTRS-SA-124    | 24.00 | 25.31   | 30.69   | 23.00 | 16.00 | 1.50    | 6.88    | 5 | 175 LBS.      |

# Strap Mounting Option

## C-230 Strap Mount




### Notes

1. To order, specify **C-230-S-2XX** see pages 14-15 for more information.
2. Strap mount slides are not designed to accommodate the standard EIA hole pattern.
3. All slides requires a .31" clearance behind the spring and button assembly for proper operation.

| A     | B     |
|-------|-------|
| 12.00 | 10.50 |
| 14.00 | 12.50 |
| 16.00 | 14.50 |
| 18.00 | 16.50 |
| 20.00 | 18.50 |
| 22.00 | 20.50 |
| 24.00 | 22.50 |

## C-300 Strap Mount




### Notes

1. To order, specify **C-300-S-2XX** see pages 16-17 for more information.
2. Strap mount slides are not designed to accommodate the standard EIA hole pattern.
3. All slides requires a .31" clearance behind the spring and button assembly for proper operation.

| A     | B     |
|-------|-------|
| 10.00 | 8.50  |
| 12.00 | 10.50 |
| 14.00 | 12.50 |
| 16.00 | 14.50 |
| 18.00 | 16.50 |
| 20.00 | 18.50 |
| 22.00 | 20.50 |
| 24.00 | 22.50 |
| 26.00 | 24.50 |
| 28.00 | 26.50 |
| 30.00 | 28.50 |

## CTS Strap Mount



### Notes

1. To order, specify **CTS-2XX** see pages 18-19 for more information.
2. Strap mount slides are not designed to accommodate the standard EIA hole pattern.
3. All slides requires a .31" clearance behind the spring and button assembly for proper operation.

| A     | B     |
|-------|-------|
| 12.00 | 10.50 |
| 14.00 | 12.50 |
| 16.00 | 14.50 |
| 18.00 | 16.50 |
| 20.00 | 18.50 |
| 22.00 | 20.50 |
| 24.00 | 22.50 |

# Optional Mounting Brackets

**Matrix For Solid Bearing Slides & Appropriate Rear Mounting Brackets with Range of Extension**

|         | B-131*   | B-131-2     | B-131-2.5   | B-131-3      | B-131-3.5    | B-131-4      | B-307-1<br>B-814-1 | B-307-2<br>B-814-2 | B-810-1   | B-810-2   |
|---------|----------|-------------|-------------|--------------|--------------|--------------|--------------------|--------------------|-----------|-----------|
| C-230-D | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 | 0 to 4.00          | 0 to 8.00          |           |           |
| C-230-S | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 | 0 to 4.00          | 0 to 8.00          |           |           |
| CTD     | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 | 0 to 4.00          | 0 to 8.00          |           |           |
| CTS     | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 | 0 to 4.00          | 0 to 8.00          |           |           |
| CTRD    | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 | 0 to 4.00          | 0 to 8.00          |           |           |
| CTRS    | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 | 0 to 4.00          | 0 to 8.00          |           |           |
| CTHD    | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 |                    |                    | 0 to 4.00 | 0 to 8.00 |
| CTHS    | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 |                    |                    | 0 to 4.00 | 0 to 8.00 |
| CTHRD   | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 |                    |                    | 0 to 4.00 | 0 to 8.00 |
| CTHRS   | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 |                    |                    | 0 to 4.00 | 0 to 8.00 |
| C-857   | 0 to .50 | .44 to 1.06 | .94 to 1.56 | 1.44 to 2.06 | 1.94 to 2.56 | 2.44 to 3.06 |                    |                    |           |           |

Note brackets are made from 16 gauge C.R.S. — Standard finish: clear zinc commercial plating

\*Supplied with standard slides

| CATALOG NUMBER | A    |  |
|----------------|------|--|
| B-131          | 1.56 |  |
| B-131-2        | 2.00 |  |
| B-131-2.5      | 2.50 |  |
| B-131-3        | 3.00 |  |
| B-131-3.5      | 3.50 |  |
| B-131-4        | 4.00 |  |

|                             |      |      |    |
|-----------------------------|------|------|----|
|                             |      |      |    |
|                             |      |      |    |
|                             |      |      |    |
| CATALOG NUMBER              | A    | B    | C  |
| B-307-1 / B-810-1 / B-814-1 | 5.94 | 4.38 | 16 |
| B-307-2 / B-810-2 / B-814-2 | 9.69 | 8.13 | 28 |