

Honeywell Sensing and Control

Search



narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6165)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (890)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1372)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)

white papers

Wireless Switches Offer
Unlimited Benefit

Basic Switches Are Not Created
Equal

Applying Precision Switches
Sensors for Medical Devices

New Ways to Measure Torque

Choosing Safety Switches

Specifying Hour Meters

Need help?

[Click here to contact us](#)

POS187313

(Home : Products : Sensors » Fiber Optics and Liquid Level Sensors » POS)



POS Series Liquid Level Sensor with Stainless-Steel housing, Output PNP NO, standard temperature range, 2 m [6.56 ft] flying lead (cable), crystal tip

Actual product
appearance may
vary.

[Sales & Service](#)[Distributor Inventory](#)[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Sensor Type	Industrial Sensor
Operating Temperature	-25 °C to 100 °C [-13 °F to 212 °F]
Housing Material	Stainless-steel
Housing Type	Industrial
Supply Voltage	12 Vdc to 28 Vdc
Output Type	PNP NO
Application Type	Variable
Termination Type	2 m [6.56 ft] flying lead (cable)
Stainless Steel Nut	Yes
Dome Dimension	12,7 [0.5 in] radius
Thread Dimension	1/2 in BSPT
Hex Dimension	34 mm [1.34 in]
Supply Current	25 mA
Output Current Sinking	200 mA max.
Availability	Global
Comment	POS Series optical liquid level sensor
UNSPSC Code	411121
UNSPSC Commodity	411121 Transducers
Series Name	POS

contacts

Customer Service
Technical Support
Global Sales & Service
View Site Demo
Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

my links

Login to iCOM
Login to Rep/AD Portal
Login to Digital University

News Center

Honeywell Introduces
TruStability® NSC Series,
Uncompensated / Unamplified
Board Mount Pressure Sensors

HONEYWELL EXPANDS ITS
LIMITLESS™ PLATFORM WITH
THE LAUNCH OF ITS
GLOBALLY AVAILABLE
INDUSTRIAL WIRELESS
RECEIVER

HONEYWELL EXTENDS ITS
TRUSTABILITY® PRESSURE
SENSOR PRODUCT LINE WITH
A SINGLE SIDE LIQUID MEDIA
OPTION

HONEYWELL ADDS NEW 100°
AND 180° ARC
CONFIGURATIONS TO ITS
SMART POSITION SENSOR
PORTFOLIO

HONEYWELL INTRODUCES
ITS HAWK™ RESOLVERS 1-
INCH SERIES, FULLY HOUSED
CONFIGURATION

HONEYWELL INTRODUCES
MICROPOWER OMNIPOLAR
DIGITAL HALL-EFFECT
SENSOR ICS WITH LOW
SUPPLY VOLTAGE AND ULTRA
LOW TYPICAL CURRENT

MICRO SWITCH
Anniversary site