





Copyright FCI.


C

D

- NOTES :
- 1- MATERIALS :
BODY : High Temp thermoplastic 30% GF, COLOR BLACK UL94 V-0
PIN : COPPER ALLOY
 - 2- 7N MIN PIN RETENTION IN EITHER DIRECTION
 - 3- RoHS COMPATIBLE PRODUCT SPECIFICATION :
a- PLATING : LF means the product is Lead Free,
2µ MIN matte Tin over 1.27µ Nickel underplating.
b- MANUFACTURING PRODUCT SPECIFICATION :
Housing will withstand exposure to 260°C peak temperature
for 30 secondes in a convection infra-red or vapor phase oven.
c- LABELLING :
Meets packaging specs as per GS-14-920
d- LEGAL STATMENT : See GS-47-0004
 - 4- PLANE REFERENCE -A- IS GENERATED BY LONG PINS TAIL ROW
WITH LOWEST AREA OF BODY.
SHORT PINS ROW TO BE FLUSH OR HIGHER 0.1 MAX ABOVE REF -A-.
 - 5- MINIMUM QUANTITY IN BLI BOX : 500



SCALE 3:1
VIEW WITH
PICK-UP CAP



RECOMMENDED PAD LAYOUT

spec ref		GS-12-652			dr	A Parrenin	2014/02/28	projection  mm 		size	A3	scale	4:1		
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	A Parrenin	2014/03/19			ecn no	ELX-B-17245-1				
ISO 406 ISO 1101					chr	D Convercey	2014/03/20								
					appr	Gert Droesbeke	2014/03/21	product family		rel level	Released				
surface  ISO 1302		linear	0.X	±0.30		title	HEADER UNSHROUDED SMT				dwg no	10112690C		rev	E
			0.XX	±0.13											
			0.XXX	±0.05											
		angular	0°	±/°	www.fci.com	cat. no.	-	Product - Customer Drw				sheet 1 of 1			