

CABLE BREAKOUT BOOT, FOUR ENTRY




Table of Dimensions, inch (mm):

PART NUMBER (See Note*)	Body ID		Leg ID		Length Recovered Min.		Rec'd. Wall Ref. (W)
	Min. Exp. (A)	Max. Rec'd (B)	Min. Exp. (C)	Max. Rec'd (D)	(E), Body	(F), Leg	
F3-9FR	0.90 (23)	0.43 (11)	0.28 (7)	0.11 (3)	2.0 (51)	0.8 (20)	0.05 (1.2)
F-23FR	1.25 (32)	0.80 (20)	0.50 (13)	0.19 (5)	2.3 (58)	1.0 (25)	0.09 (2.3)
F42-60FR	1.75 (44)	0.98 (25)	0.79 (20)	0.26 (7)	2.3 (58)	1.2 (30)	0.14 (3.6)
F75-100FR	2.35 (60)	1.00 (25)	1.00 (25)	0.35 (9)	2.8 (71)	1.7 (43)	0.14 (3.6)
F133-200FR	2.65 (67)	1.40 (36)	1.20 (30)	0.53 (13)	3.5 (89)	1.5 (38)	0.14 (3.6)
F150-400FR	5.25 (133)	3.00 (76)	1.35 (34)	0.55 (14)	5.0 (127)	3.0 (76)	0.13 (3.3)

Note*: Add "NA" to the end of Part Number if no adhesive is required.

Material: Heat shrinkable boot material in accordance with –3 polyolefin

Factory applied sealant: Factory applied hot melt adhesive is standard.

Raychem Products, North America Tyco Electronics Corporation 300 Constitution Drive Menlo Park, CA 94025 USA		Product Brand: Raychem				
Specification Control Drawing		Title: CABLE BREAKOUT BOOT, FOUR ENTRY				
		Size A	Cage Code 06090	Document No. FXXX-XXXFR		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. METRIC DIMENSIONS ARE SHOWN IN BRACKETS		Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.		Rev.: B	Rev. Date: 25-Mar-03	
Drawn By: A.Ng	Org. Date: 03/17/03	Original file:		File : R030156.doc	Scale: None	Sheet: 1 of 1

If this document is printed it becomes uncontrolled. Check for the latest revision.