






RECOMMENDED HOLE LAYOUT FOR 1.78 [.070] MAXIMUM THICK PC BOARD.



- 1 MATERIAL: HOUSING-NYLON, UL94V-2
(COLOR-NATURAL, COLOR OF PARTS MAY VARY).
CONTACTS-0.25 [.010] THICK BRASS ALLOY
- 2 CONTACT FINISH: 0.000100 [.0000039] MIN. MATTE TIN
OVER 0.000050 [.0000020] MIN. NICKEL OVER ENTIRE
CONTACT.
- 3 MATES WITH VAL-U-LOK(TM) RECEPTACLE HOUSINGS.

59.4 [2.32]	57.0 [2.24]	55.6 [2.19]	51.6 [2.03]	46.2 [1.82]	24	2-1586585-4
55.2 [2.17]	52.0 [2.08]	51.4 [2.02]	47.4 [1.87]	42.0 [1.65]	22	2-1586585-2
51.0 [2.01]	48.6 [1.91]	47.2 [1.86]	43.2 [1.70]	37.8 [1.49]	20	2-1586585-0
46.8 [1.84]	44.4 [1.75]	43.0 [1.69]	39.0 [1.54]	33.6 [1.32]	18	1-1586585-8
42.6 [1.69]	40.2 [1.58]	38.8 [1.53]	34.8 [1.37]	29.4 [1.58]	16	1-1586585-6
38.4 [1.51]	36.0 [1.42]	34.6 [1.36]	30.6 [1.20]	25.2 [0.99]	14	1-1586585-4
34.2 [1.35]	31.8 [1.25]	30.4 [1.20]	26.4 [1.04]	21.0 [0.83]	12	1-1586585-2
30.0 [1.18]	27.6 [1.09]	26.2 [1.03]	22.2 [0.87]	16.8 [0.66]	10	1-1586585-0
25.8 [1.02]	23.4 [0.92]	22.0 [0.87]	18.0 [0.71]	12.6 [0.50]	8	1586585-8
21.6 [0.85]	19.2 [0.76]	17.8 [0.70]	13.8 [0.54]	8.4 [0.33]	6	1586585-6
17.4 [0.69]	15.0 [0.59]	13.6 [0.54]	9.6 [0.38]	4.2 [0.17]	4	1586585-4
13.2 [0.52]	10.8 [0.43]	9.4 [0.37]	5.4 [0.21]	—	2	1586585-2
(E)	(D)	C	B	(A)	POS	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN. S. HOOVER 12-NOV-2004 CHK. D. COLEY 12-NOV-2004 APP'D. D. COLEY 12-NOV-2004		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± 1 PLC ± 2 PLC ± 0.13 [0.005] 3 PLC ± 4 PLC ± 5 ANGLE'S ± 0°30' FINISH		VERTICAL HEADER ASSEMBLY – BLINDMATE WITH DRAIN HOLES, VAL-U-LOK(TM)	
MATERIAL		APPLICATION SPEC		RESTRICTED TO	
WEIGHT		SIZE		CAGE CODE	
CUSTOMER DRAWING		DRAWING NO		A1 00779 C 1586585	
SCALE		SHEET		REV	
5:1		1 of 1		A	