

FLK 40/4X14/EZ-DR/ 200/IB32

Order No.: 2296838



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2296838>

Round cable set, for connection to Allen Bradley SLC 500, OB 32 and IB 32, with one 40-position socket strip and four 14-position socket strips, for splitting 32 channels into 4x8 channels, for IB 32, no. of positions 40/4x14, cable length 2.0 m

Commercial data

EAN	4017918612863
Pack	1 pcs.
Customs tariff	85444290
Weight/Piece	0.4244 KG
Catalog page information	Page 194 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
10/01/2005



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. conductor resistance	0.16 Ω /m

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Number of positions, control side	40
Number of connectors, control side	1
Number of positions, module side	14
Number of connectors, modul side	4
Fixed cable length	2 m
Single wire, cross section	0.14 mm ²
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	7.8 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no

Certificates / Approvals



Certification

GOST

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;