

**NEW
PRODUCT**



SPECIFICATIONS

Contact Rating:	12VDC, 50mA
Life Expectancy:	100,000 cycles minimum
Contact Resistance:	100mΩ max., 100MΩ min.
Insulation Resistance:	10000 MΩ min.
Dielectric Strength:	250 VAC
Actuator Force:	180 ± 50 gf min.
Operating Temperature:	-20°C to +70°C
Storage Temperature:	-40°C to +80°C

MATERIALS

Housing:	Nylon 46
Actuator:	Nylon 46
Cover:	Stainless Steel
Contacts:	Stainless Steel
Terminals:	Brass
Travel:	0.30 +/- 0.10mm
Tape & Reel:	3000 pieces per reel

HOW TO ORDER

Series	Model No.	Boss	Operating Force	Contact Material	Termination
TL	1014	A	F	Q	G
TL	1014	A=no boss B=boss	F180	Q=Silver	G= Gull

EXAMPLE

TL → 1014 → A → F180 → Q → G

ACTUATOR LENGTH

TL 1014 Boss
A= no boss
A= boss