

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		D9	REVISED PER ECO-12-012202	03JUL12	KH	MS

5	2	104.7	112.2	—	—	10	4-1546307-7	
5	2	104.7	112.2	—	—	10	4-1546307-6	
5	4	104.7	112.2	—	—	10	4-1546307-5	
5	2	1	104.7	112.2	—	10	3-1546307-3	
		104.7	112.2	—	—	10	1-1546307-0	
5	3	2	1	95.2	102.7	—	9	5-1546307-0
5	3	2	1	95.2	102.7	4	9	4-1546307-9
3	2	1	95.2	102.7	4	9	9	4-1546307-8
		95.2	102.7	—	—	9		1546307-9
		85.7	93.2	—	—	8		1546307-8
		76.2	83.7	—	—	7		1546307-7
5	4	66.7	74.2	—	—	6		4-1546307-4
		66.7	74.2	—	—	6		1546307-6
5	2	57.2	64.7	—	—	5		4-1546307-3
5	2	57.2	64.7	—	—	5		4-1546307-2
5	2	57.2	64.7	—	—	5		4-1546307-1
5	2	57.2	64.7	—	—	5		4-1546307-0
5	4	57.2	64.7	—	—	5		3-1546307-9
		57.2	64.7	—	—	5		1546307-5
5	2	1	47.7	55.2	—	—	4	3-1546307-2
		47.7	55.2	—	—	4		1546307-4
5	2	38.2	45.7	—	—	3		3-1546307-8
5	2	38.2	45.7	—	—	3		3-1546307-7
5	2	38.2	45.7	—	—	3		3-1546307-6
5	2	38.2	45.7	—	—	3		3-1546307-5
5	4	38.2	45.7	—	—	3		3-1546307-4
		38.2	45.7	—	—	3		1546307-3
		28.7	36.2	—	—	2		1546307-2
		DIM B	DIM A	QC TAB .187 45° ②	QC TAB .187 FLAT ①	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 20AUG2002	STE TE Connectivity										
		CHK C RICHARD 8/20/02											
		APVD C RICHARD 8/20/02											
		PRODUCT SPEC											
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 9.50MM (.374) DBL ROW BARRIER STRIP W/ WASHER									
		0 PLC ± — 1 PLC ± 0.3 2 PLC ± 0.25 3 PLC ± — 4 PLC ± — ANGLES ± 2°											
MATERIAL —		FINISH —		APPLICATION SPEC —		SIZE A3		CAGE CODE 00779		DRAWING NO C-1546307		RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 1:1		SHEET 1 OF 3		REV D9			

PHYSICAL PROPERTIES:
HOUSING MATERIAL: PBT
FLAMMABILITY: UL94V-0
COLOR: BLACK

TERMINAL:
TERMINALS: BRASS, TIN PLATED
SCREWS: 6-32, STEEL, NICKEL PLATED

MECHANICAL:
PITCH (TERMINAL SPACING): 9.50mm (.374")
WIRE RANGE: 12-22 AWG
RECOMMENDED TIGHTENING TORQUE: 12IN-LBS MAX.

ELECTRICAL PROPERTIES:
MAXIMUM CURRENT: 20A
OPERATING VOLTAGE: 300V

ENVIRONMENTAL PROPERTIES:
OPERATING TEMP RANGE: -40°C TO 120°C

- 1
- SCREWS ON ONE SIDE IN WIRE READY POSITION.

2

3

4

5

6


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


ALL RIGHTS RESERVED.

© COPYRIGHT - By -



LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—





3-1546307-1





3-1546307-2





3-1546307-3




3-1546307-7






3-1546307-8



3-1546307-6



3-1546307-5



294.7	302.2	—	—	30	3-1546307-0
285.2	292.7	—	—	29	2-1546307-9
275.7	283.2	—	—	28	2-1546307-8
266.2	273.7	—	—	27	2-1546307-7
256.7	264.2	—	—	26	2-1546307-6
247.2	254.7	—	—	25	2-1546307-5
237.7	245.2	—	—	24	2-1546307-4
228.2	235.7	—	—	23	2-1546307-3
218.7	226.2	—	—	22	2-1546307-2
209.2	216.7	—	—	21	2-1546307-1
199.7	207.2	—	—	20	3-1546307-1
199.7	207.2	—	—	20	2-1546307-0
190.2	197.7	—	—	19	1-1546307-9
180.7	188.2	—	—	18	1-1546307-8
171.2	178.7	—	—	17	1-1546307-7
161.7	169.2	—	—	16	1-1546307-6
152.2	159.7	—	—	15	1-1546307-5
142.7	150.2	—	—	14	1-1546307-4
133.2	140.7	—	—	13	1-1546307-3
123.7	131.2	—	—	12	1-1546307-2
114.2	121.7	—	—	11	1-1546307-1
DIM B	DIM A	QC TAB .187 45° ②	QC TAB .187 FLAT ①	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± 0.3
2 PLC ± 0.25
3 PLC ± —
4 PLC ± —
ANGLES ± 2°
FINISH —

DWN S SCHLEGEL 20AUG2002
CHK C RICHARD 8/20/02
APVD C RICHARD 8/20/02
PRODUCT SPEC
APPLICATION SPEC
WEIGHT —

9.50MM (.374) DBL ROW BARRIER STRIP
W/ WASHER

SIZE A3
CAGE CODE 00779
DRAWING NO C-1546307

CUSTOMER DRAWING

TE Connectivity

RESTRICTED TO —

SCALE 1:1
SHEET 2 OF 3
REV D9

4

3

2


1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
-	-	-	-	SEE SHEET 1	-	-




4-1546307-2




4-1546307-3




4-1546307-7




4-1546307-6




4-1546307-0




4-1546307-1




4-1546307-8




MARK BOTH SIDES




4-1546307-9



MARK BOTH SIDES




5-1546307-0



MARK BOTH SIDES

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 20AUG2002	 TE Connectivity			
		CHK C RICHARD 8/20/02				
		APVD C RICHARD 8/20/02	NAME 9.50MM (.374) DBL ROW BARRIER STRIP W/ WASHER			
		PRODUCT SPEC			SIZE A3	CAGE CODE 00779
		APPLICATION SPEC			DRAWING NO C-1546307	RESTRICTED TO -
		WEIGHT -				
CUSTOMER DRAWING				SCALE 1:1	SHEET 3 OF 3	REV D9

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC ± -	
		1 PLC ± 0.3	
		2 PLC ± 0.25	
		3 PLC ± -	
		4 PLC ± -	
		ANGLES ± 2°	
MATERIAL -		FINISH -	