







LOC		DIST		REVISIONS					
FT			0	P	LTR	DESCRIPTION	DATE	DWN	APVD
				P		ADDED 1-2, 1-3 ECO-06-002610	15FEB2006	SW	SH
				P	I	REVISED PER ECO-09-025699	12DEC2009	KK	AEG



- △ HOUSING: NYLON, UL 94 V-0 RATED, BLACK.
- △ CONTACT:
BODY - BRASS, .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
- △ CONTACT:
BODY - BRASS, .000100 MIN TIN OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN OVER .000050 MIN NICKEL.
- △ PERIPHERAL SEAL: ELASTOMER, GRAY.
- △ KEYING PLUG: NYLON, NATURAL.
- △ .009 MAXIMUM CONTACT LEAD-IN SEAM GAP PERMISSIBLE
ON MATING FACE END.
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



7	POSN 9	YES	3	8	1-8	1-213826-3
7	-	YES	3	8	1-5, 7-9	1-213826-2
	-	YES	3	9	ALL	1-213826-1
7	POSN 9	YES	3	8	1-8	1-213826-0
7	-	YES	3	8	1-5, 7-9	213826-9
	POSN 9	YES	2	8	1-8	213826-8
	-	YES	2	8	1-5, 7-9	213826-7
7	POSN 9	YES	2	8	1-8	213826-3
7	-	YES	2	8	1-5, 7-9	213826-2
	-	YES	2	9	ALL	213826-1
KEYING PLUG		PERIPHERAL SEAL	FINISH	QTY	SELECT LOAD IN POSITIONS	PART NUMBER
			CONTACTS			

RECOMMENDED PC BOARD LAYOUT
SCALE 3:1

RECOMMENDED PANEL LAYOUT
.125 MAX PANEL THICKNESS
SCALE 3:1

DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN S. WELDON 23MAY2003		Tyco Electronics Harrisburg, PA 17105-3608	
9 PLC ±.0		2 PLC ±0.00		CHK S. HEADER 23MAY2003		NAME RECEPTACLE ASSEMBLY, POSTED, REVERSE SEX, SERIES 1, 17-9, CPC	
3 PLC ±0.010		4 PLC ±0.0000		APVD S. HEADER 23MAY2003		SIZE 108-10024	
MATERIAL		FINISH		PRODUCT SPEC		APPLICATION SPEC	
				114-10004		WEIGHT	
				CUSTOMER DRAWING		A1 00779 C=213826	
						SCALE 4:1 SHEET 1 OF 1 REV P1	