




NICKEL CADMIUM BATTERIES: INDIVIDUAL DATA SHEET

P-50AAH (AA) size Type: H

Dimensions (with tube) (mm)



Typical Charge Characteristics



Specifications

	mm	inch
Diameter	14.5 +0 / -0.7	0.57 +0 / -0.03
Height	50.0 +0 / -1.0	1.97 +0 / -0.04
Approximate Weight	Grams	Ounces
	21g	0.74


Nominal Voltage		1.2V	
Discharge Capacity*	Average**	580mAh	
	Rated (Min.)	500mAh	
Approx. Internal impedance at 1000Hz at charged state.		20mΩ	
Charge	Standard	50mA (0.1C) x 16hrs.	
	Trickle	Max Current	25mA (0.05C) x 30h and over
		Min Current	17mA (0.033C) x 45h and over
Ambient Temperature	Charge		°C
			0°C to 50°C
			32°F to 122°F
	Discharge		-20°C to 65°C
Storage	< 2 years		-20°C to 35°C
	< 6 months		-20°C to 45°C
			-4°F to 113°F

* 0.2C discharge capacity after charging at 0.1C for 16 hours.

** For reference only.

Battery performance and cycle life are strongly affected by how they are used. In order to maximize battery safety, please consult Panasonic when determining charge / discharge specs, warning label contents and unit design.

Typical Discharge Characteristics



Panasonic

NICKEL CADMIUM

This information is generally descriptive only and is not intended to make or imply any representation, guarantee or warranty with respect to any cells and batteries. Cell and battery designs/specifications are subject to modification without notice. Contact Panasonic for the latest information.