




PRODUCT NUMBER
SEE TABLE



SEE SHEET 3 FOR
LOCATOR/HOLDDOWN
VARIATIONS

.014 [0.36]
AT TIPS



mat'l. code				surface		tolerance		projection	product family					
-				ISO 1302 ✓		ISO 406 ISO 1101			RIBCAGE					
ltr	ecn no	dr	date	tolerances unless otherwise specified						title RIBCAGE III T/M VERT. HEADER ASS'Y				
L	J10329	CRG	6/6/01	angles	linear	.XX±.01/0.3							INCH/MM	
M	M05-0123	MHT	6/6/05			.XXX±.005/0.13								
N	M06-0225	ERE	06/12/06			.XXXX±.0020/0.051								
P	M06-0370	MHT	9/26/06	0±2°		scale 4:1				dwg no			sheet 1 of 6	size
R	M09-0058	MHT	4/04/09	enrg	D. WHITING	6/6/95		95776		A3				
S	N10-0122	YO	5/10/10	chr	D. WHITING	6/6/95								
T	ELX-N-009749	YO	1/31/12	appd	D. WHITING	6/6/95								
											type			Product
sheet	revision		T	T	T	T	T	T						
index	sheet		1	2	3	4	5	6						




FCIconnect.com


Copyright FCI

PRODUCT NUMBER
SEE TABLE

SIZE	DIM H	DIM J	DIM K	DIM L
2X5	.275/6.99	.200/5.08	.372/9.45	.320/8.13
2X10	.525/13.34	.450/11.43	.622/15.80	.570/14.48
2X15	.775/19.68	.700/17.78	.872/22.15	.820/20.83
2X20	1.025/26.03	.950/24.13	1.122/28.50	1.070/27.18
2X25	1.275/32.38	1.200/30.48	1.372/34.85	1.320/33.53
2X30	1.525/38.74	1.450/36.83	1.622/41.20	1.570/39.88
2X35	1.775/45.08	1.700/43.18	1.872/47.55	1.820/46.23
2X40	2.025/51.43	1.950/49.53	2.122/53.90	2.070/52.58
2X45	2.275/57.78	2.200/55.88	2.372/60.25	2.320/58.93
2X50	2.525/64.14	2.450/62.23	2.622/66.60	2.570/65.28



SECTION X-X
ROTATED 90° CW




SECTION Y-Y

mat'l. code -					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																		
ltr	ecn	no	dr	date	tolerances unless otherwise specified							title																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																	
T					angles		linear	.XX±.01/0.3 .XXX±.005/0.13 0氣2? .XXXX±.0020/0.051		INCH/MM		RIBCAGE III T/M VERT. HEADER ASS'Y																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																	
										scale 4:1																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																			
					dr	M. CORNMAN	6/6/95										dwg no	sheet2 of 6			size																																																																																																																																																																																																																																																																																																																																																																																																																																																																																								
					enrg	D. WHITING	6/6/95										95776	A3																																																																																																																																																																																																																																																																																																																																																																																																																																																																																											
					chr	D. WHITING	6/6/95																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
					appd	D. WHITING	6/6/95																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																						


PRODUCT NUMBER
SEE TABLE

LOCATOR/HOLDDOWN VARIATIONS

STYLE
1




STYLE
2





(ALL PEG CONFIGURATIONS)


STYLE
4



STYLE
6



STYLE
7




mat'l. code -					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE					
ltr	ecn	no	dr	date	tolerances unless otherwise specified							title				
T					angles	linear	.XX±.01/0.3					INCH/MM				
							.XXX±.005/0.13					RIBCAGE III T/M VERT. HEADER ASS'Y				
					0.002		.XXXX±.0020/0.051									
					dr	M. CORNMAN	6/6/95				dwg no		sheet 3 of 6		size	
					enr	D. WHITING	6/6/95				95776		A3			
					chr	D. WHITING	6/6/95				type Product Customer Drawing					
					appd	D. WHITING	6/6/95									
sheet index		revision sheet														


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
6




STYLE
2



STYLE
7



STYLE
4




mat'l. code -					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE									
ltr ecn no dr date					tolerances unless otherwise specified					INCH/MM		title RIBCAGE III T/M VERT. HEADER ASS'Y								
T					angles		linear													
							.XX±.01/0.3													
							.XXX±.005/0.13													
					0氣2?		.XXXX±.0020/0.051			scale 4:1		dwg no sheet4 of 6 size 95776 A3								
					dr		M. CORNMAN		6/6/95											
					enrg		D. WHITING		6/6/95											
					chr		D. WHITING		6/6/95											
					appd		D. WHITING		6/6/95		FCI 		type Product Customer Drawing							
sheet index		revision sheet																		


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
2



STYLE
4



STYLE
6



mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 	product family RIBCAGE	
ltr	ecn	no	dr	date	tolerances unless otherwise specified				title	
T					angles	linear	.XX±.01/0.3	INCH/MM	RIBCAGE III T/M VERT. HEADER ASS'Y	
					0氣2?		.XXX±.005/0.13			
							.XXXX±.0020/0.051	scale 4:1	dwg no sheet 5 of 6 size	
					dr	M. CORNMAN	6/6/95		95776	
					enrg	D. WHITING	6/6/95		A3	
					chr	D. WHITING	6/6/95			
					appd	D. WHITING	6/6/95		type Product Customer Drawing	
sheet index	revision sheet									

