



PRODUCTS

INDUSTRY SOLUTIONS

CAREERS

RESOURCES


CONTACT MOLEX

FIND DISTRIBUTOR

Home: Ring and Spade Terminals >

Part Number: 50856-7312

Ring Tongue Terminal for 10 and 12 AWG, Closed Un-insulated Brazed Barrel, Stud Size 6 (M3.5), Oxygen Free Copper, Length 18.30mm



Series image - Reference only

Status:
Replacement:OBsolete
Contact MolexSeries:
Category:50856
Ring and Spade Terminals

CHECK DISTRIBUTOR INVENTORY

 Add to My Parts
 Email this pageGo to [Part Detail](#) ▾**Product Environmental Compliance**[EU ELV](#): Product not active[EU RoHS](#): Product not active[EU RoHS Phthalates](#): Product not active[China RoHS](#):[REACH SVHC](#): Product not active[Low-Halogen Status](#): Product not active

EU RoHS Certificate of Compliance (PDF)

 Multiple Part Product Compliance Statements
EU RoHS, REACH SVHC, & Low-Halogen Multiple Part Industry Compliance Documents
*IPC 1752A Class C
*IPC 1752A Class D
*Molex Product Compliance Declaration**Application Tooling****FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Japan

Description	Product #
Hand Crimper For JIS Terminal	57257-5000
Air Type Hand Crimper For JIS Terminal	57343-9005

Crimp Quality Equipment

Molex also offers wire strippers, pull testers, shut-height gauges, micrometers and more

Previously Available Application Tooling

Check our list of old tooling that used to be available for this part

Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail**[COLLAPSE ALL](#)**▼ General**

Status	Obsolete
Category	Ring and Spade Terminals
Series	50856
Mil-Spec	N/A
Product Name	R (Ring)
Type	Ring
UPC	800754838221

▼ Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	1435.000/mg
Packaging Type	Bag
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Stud Size	6 (M3.5)
Termination Interface: Style	Crimp or Compression
Wire Size AWG	10, 12
Wire Size mm ²	2.63-6.64

▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number.

[Click here to visit the UL Database](#)

CSA	LR95446
UL	E134962

PRODUCTS**QUICK LINKS****RESOURCES****STAY CONNECTED**

Antennas
Application Tooling
Cable Assemblies
Connected Lighting
Connectors
Copper Flex
Electrical Products
Industrial Automation
Membrane Switches
Optical Solutions
Printed Electronic Solutions

Company Information
Contact Molex
Cross-Reference
Koch Industries
Industries
Investor Relations
Literature
Molex Racing
Press Room / Press Releases
Product Index
Sitemap
Terms & Conditions

Supply Chain Transparency
Business Continuity
Compliance
ecocare
Feedback | Help
Jobs
Legal | Trademarks
Mobile Site
Supplier Portal
Privacy Policy
Tradeshows

