












PRODUCT NO.
10029449-X01XLF



SECTION A-A

mat'l. code				surface		tolerance	projection	product family	
ltr ecn nodr date				ISO1302		ISO1101 ISO406	MM	HDMI	
M N09-0307 SH 10/21/09				N N10-0033 SH 02/01/10		.X±0.3	MM	HDMI TYPE A RECEPTACLE	
P N10-0201 KW 2011-02-14				R N12-0001 SH 2012-02-23		.XX±0.15	scale 4.0	dwg no sheet 1 of 5 size	
S N12-0003 AZH 2012-06-13				dr LEIF SHEN 10/15/04		.XXX±0.05	FCI	10029449 A4	
				enr LEIF SHEN 10/15/04				type Product Customer Drawing	
				chr PAUL WANG 10/15/04					
				app JOSEPH HSIA 10/15/04					
sheet	revisions	s	s	s	s				
index	sheet	1	2	3	4	5			

PRODUCT NO.
10029449-002XLF



mat'l. code				surface		tolerance		projection		product family			
				ISO1302 ✓		ISO1101 ISO406				HDMI			
ltr		ecn		nodr		date		tolerances unless otherwise specified				title	
M		N09-0307		SH		10/21/09				HDMI TYPE A RECEPTACLE			
N		N10-0033		SH		02/01/10							
P		N10-0201		KW		2011-02-14							
						0'±2"		scale 4.0					
R		N12-0001		SH		2012-03-09		dr		LEIF SHEN		10/15/04	
S		N12-0003		A.ZH		2012-06-13		engr		LEIF SHEN		10/15/04	
								chr		PAUL WANG		10/15/04	
								app		JOSEPH HSIA		10/15/04	
sheet		revision											
index		sheet											



[illegible]

6. PARTS MEET REFLOW APPLICATION PEAK TEM. 260°C, 10 SECONDS MAX.

Printed: Jun 15, 2012⁴

PRODUCT NO.	CONTACT AREA PLATING	SHIELD FIGURE	DIM "A"	PACKING
10029449-111RLF	GOLD FLASH 3u" MIN	WITHOUT FLANGE	2.02±0.20	TAPE AND REEL
10029449-113RLF	GOLD FLASH 3u" MIN	WITHOUT FLANGE	0.90±0.20	TAPE AND REEL

NOTE:

1.MATERIAL:

HOUSING: HIGH TEMP.THERMOPLASTIC, UL 94V-0

COLOR: BLACK.

CONTACT: PHOSPHOR BRONZE







SHIELD: BRASS

2.FINISH:

SEE NOTES.

3.TERMINAL RETENTION FORCE TO BE 0.3kgf MIN.

4.TERMINAL CUT-OFF BURR TO BE 0.05MAX.



mat'l. code				surface ISO1302 ✓		tolerance ISO1101 ISO406		projection 		product family HDMI						
ltr		ecn		nodr		date		tolerances unless otherwise specified		title						
M	N09-0307		SH		10/21/09		angle linear 0°±2'	.X±0.3				HDMI TYPE A RECEPTACLE				
N	N10-0033		SH		02/01/10			.XX±0.15								
P	N10-0201		KW		2011-02-14			.XXX±0.05								
R	N12-0001		SH		2012-03-09		dr	LEIF SHEN	10/15/04		dwg no		sheet4 of 5		size	
S	N12-0003		A.ZH		2012-06-13		engr	LEIF SHEN	10/15/04							
							chr	PAUL WANG	10/15/04							
							app	JOSEPH HSIA	10/15/04				type		Product Customer Drawing	
sheet		revision														
index		sheet														

Printed: Jun 15, 2012⁴