

A102 HSS Quick Spiral Jobber Drills



DIN 338 RW/BS 328
Flute geometry - Thick helix, extra wide flutes, narrow lands
Point angle - 118°
Surface treatment - Bright
Range - 1-10mm
Application - For drilling Aluminium, Magnesium, Copper and other light alloys.

492771

Size (mm)	Flute Length (mm)	Overall Length (mm)	Order Code	Price Each
1.00	12	34	137-5655	
2.00	24	49	137-5656	
2.50	30	57	137-5657	
3.00	33	61	137-5658	
3.30	36	65	137-5661	
3.50	39	70	137-5662	
4.00	48	75	137-5663	
5.50	57	93	137-5664	