




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		B2	REVISED PER ECR-15-012046	15JUN2015	I.T	W.H

D




TERMINATED VIEW

C





A




- 1 MOLDED PARTS: UL RATED 94V-0 THERMOPLASTIC, BLACK.
- 2 CONTACTS: PHOSPHOR BRONZE PER QQ-B-750.
- 3 CONTACTS: PLATED WITH .000030 MIN GOLD IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
OR
GOLD FLASH OVER PALLADIUM-NICKEL PLATE .000030 MIN TOTAL IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMENATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
- 4 POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSN #1 INDICATOR ON 10 AND 14 POSN PRODUCT.

LOCALIZED GOLD PLATING ON THIS SURFACE

.014 MIN LOCALIZED GOLD PLATE AREA 3



1.125	2.100	2.380	2.150	43	44	1-1658622-3
1.625	3.100	3.380	3.150	63	64	1-1658622-2
1.525	2.900	3.180	2.950	59	60	1-1658622-1
1.275	2.400	2.680	2.450	49	50	1-1658622-0
1.025	1.900	2.180	1.950	39	40	1658622-9
.875	1.600	1.880	1.650	33	34	1658622-8
.775	1.400	1.680	1.450	29	30	1658622-7
.675	1.200	1.480	1.250	25	26	1658622-6
.625	1.100	1.380	1.150	23	24	1658622-5
.525	.900	1.180	.950	19	20	1658622-4
.425	.700	.980	.750	15	16	1658622-3
.375	.600	.880	.650	13	14	1658622-2
.275	.400	.680	.450	9	10	1658622-1
E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. SAMICK 22AUG03		 TE Connectivity							
			CHK C. RHODE 22AUG03									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY 22AUG03		NAME						
		0 PLC ± -		PRODUCT SPEC		RECEPTACLE ASSY, CENTER & MILITARY POLARIZATION LEAD FREE AMP-LATCH™ NOVO						
		1 PLC ± -		108-40000								
		2 PLC ± -		APPLICATION SPEC								
		3 PLC ± .005		114-40005								
4 PLC ± -		ANGLES ± 5°		WEIGHT -		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL		FINISH		A2		00779		C-1658622		-		
SEE NOTES		SEE NOTES		CUSTOMER DRAWING						SCALE 4:1	SHEET 1 of 2	REV B2

4



3

2

1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	APVD
		-	-	SEE SHEET 1	-	-



1-1658622-2	9-1658622-2
SUB CONNECTOR	REEL PACKAGED PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. SAMICK	22AUG03	 TE Connectivity							
DIMENSIONS: INCHES			CHK C. RHODE	22AUG03								
	TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD M. WALMSLEY	22AUG03	NAME RECEPTACLE ASSY, CENTER & MILITARY POLARIZATION LEAD FREE AMP-LATCH NOVO						
	0 PLC ± -			PRODUCT SPEC								
	1 PLC ± -			108-40000								
	2 PLC ± -			APPLICATION SPEC								
	3 PLC ± .005			114-40005								
4 PLC ± -			WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
MATERIAL			FINISH			A2		00779	C=1658622	-		
SEE NOTES			SEE NOTES			CUSTOMER DRAWING						
						SCALE		4:1	SHEET	2 of 2	REV	B2