


LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
		F		REVISED PER ECR-09-020122	24SEP09	APVD



AMP WIRE RANGE	UL Listed FILE E13288	LR7189 Certified
4 AWG SOLID OR STRANDED	4 AWG STRANDED	4 AWG SOLID OR STRANDED

- 1

STAMP AMP 4* APPROX AS SHOWN
- 2

TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B-545
- 3

GOLD PLATE 0.000076 [.000003] MIN THK PER ASTM B-488, TYPE 2, CODE C, OVER NICKEL PLATE, 0.00127 [.000050] MIN THK PER QQ-N-290.
- 4

COPPER PER ASTM B-152, ANNEALED
- 5

PRELIMINARY - NOT FOR PRODUCTION

3	5	320743-1
2		320743
FINISH		PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 16.8-26.7mm² [33,100-52,600] SOLID OR STRANDED
TOOLING INFORMATION		
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-29-93	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm[INCHES]		CHK DA PATTERSON 3-29-93				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JL MECKLEY 3-29-93	NAME TERMINAL, RING, TONGUE, SOLISTRAND			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC — APPLICATION SPEC —	SIZE A2			
MATERIAL 4		FINISH SEE TABLE	CAGE CODE 00779			
			DRAWING NO C-320743			
			RESTRICTED TO —			
			SCALE 4:1			
			SHEET 1 of 1			
			REV F			
			CUSTOMER DRAWING			