



TRIPLETT

Test Equipment & Tools



POCKET REFERENCE


TPAL-001
Professional AutoLoader

Autoloading Screwdriver w/6 selectable bits contained in a heavy duty steel shaft

- 3 Philips and 3 standard bits are pre-Loaded
- Magnetized shaft
- Bits are interchangeable with any standard 1/4" drive bit

TMAL-001
Mini AutoLoader

Autoloading Screwdriver with 6 self contained Precision bits

- 3 Philips and 3 standard bits are pre-Loaded
- Magnetized shaft
- Bits are replaceable


TBK-001
Industrial Bit Kit

32 piece Industrial Grade, 1/4" bit kit made of S2 steel

- All bits fit the Professional AutoLoader for replacement or substitution
- Kit includes: 30 S2 Steel Bits, quick release drill adapter, hex to socket adapter, carrying case w/ belt clip


TSBK-001
Security Bit Kit

32 piece Industrial Grade, 1/4" bit kit for tamper proof fasteners

- All bits fit the Professional AutoLoader for replacement or substitution
- Kit includes: 30 S2 Steel Bits, quick release drill adapter, hex to socket adapter, carrying case w/ belt clip



**TT-220****7" KlikGrip**

7" auto adjusting pliers

- Adjusts with only one hand
- Lightweight, strong and versatile
- Non-slip handles

TT-221**10" KlikGrip**

10" auto adjusting pliers

- Adjusts with only one hand
- Lightweight, strong and versatile
- Non-slip handles

**TT-230****PowrJaw Electrician's Pliers**

8" Electrician's Pliers with Ergonomic Cushion Grips


- PowrJaw delivers 100% gain in gripping power
- High Strength CRV Jaws
- Pearl nickel finish resists corrosion
- Spring loaded and lockable handles

TT-231**PowrJaw Diagonal Pliers**

7.5" Diagonal Cutting Pliers with Ergonomic Cushion grips

- PowrJaw delivers 100% gain in cutting power
- High Strength CRV Jaws
- Pearl nickel finish resists corrosion
- Spring loaded and lockable handles




TT-200
LongLockers

Extended reach 15" Locking pliers with cushioned grips

- Universal jaw design fits any application
- Narrow jaws fit into tight spaces
- Standard grip size makes operation easy

9610
Plug-Bug 2

GFCI Receptacle Tester

- Detects common wiring problems
- Push button GFCI test
- Easy to follow graphic explains how to read fault codes


PT12
ProTemp 12

Non-Contact 12:1 Infrared Thermometer

- Single handed, fast and accurate temperature readings
- Laser pinpoints measurement area
- Backlit display makes reading measurements easy

TLT-160
LaserTape 160

Non-Contact Laser Measurement
from 2"-160' accurate to 0.060"

- Easily calculate square footage, volume, and simple trig functions
- Add or subtract measurements
- 20 memory locations to save measurements




TT-110
GrabLite

6 High Intensity LED's
and 21" Telescoping Flex End Magnet

- Rare earth magnet allows for greater lifting capacity
- Runs on only 1-AA battery
- Wrist strap and carrying case included

TT-120
ClipLite

Cap Light with High Intensity White and Red LEDs
and adjustable position

- Over visor design won't impair vision
- Adjustable angle puts light where it's needed
- Flashing LEDs improve safety for joggers


TT-130
BugLite

Magnetic Base Multi-purpose light



- 2 high powered LEDs
- Hi strength Neodymium Magnetic base attaches to flats, curves, or corners
- Attaches directly to tools
- Lightweight tough aluminum body

TT-101
FUEZR

Multi-purpose LED Work Lite w/case

- 27 Bright white LEDs
- Selectable 24 LED Flood light or 3 LED Flashlight
- SilkGrip Non Slip Finish
- Self storing Hanger and adjustable stand
- 3 axis Magnet arrangement to attach to metal




8000
CamView PTZ

Multi-Function Test Tool for CCTV & Security Installers

- Full color 2.6" TFT-LCD Video Monitor
- Supports RS-485, RS-422 & RS-232 PTZ interfaces
- Supports more than 25 PTZ Protocols
- 10 hour rechargeable battery

8050
CamView W35

 Security Wrist Monitor
 with 3.5" Display

- View camera output to adjust zoom, focus, position, etc.
- Verify quality of video signal
- High Brightness, daylight viewable display
- 6 hour rechargeable battery


8105
CobraCam USB 2

Portable Inspection Camera with USB Interface

- Waterproof snake – bend to fit any application
- New ZOOM function
- Snapshot and Live Video capable
- Works with Windows OS

**Not MAC compatible*

8115
CobraCam 2

 Portable, Self Contained, Inspection Camera
 and Video Monitor

- 6' Flexible snake allows access to hidden locations
- 2 high intensity LED's for lighting
- Extend up to 100 feet of watertight length



CC2-CAM3FM**3' x 5.5mm Camera**

3' snake with 5.5mm camera head for CobraCam2



- 5.5mm head fits into small areas
- Super flexible 3 foot snake is easier to control
- Self-contained LED lighting
- Water proof connections

CC2-CAM3F**3' x 10.2mm Camera**

3' snake with 10.2mm camera head for CobraCam2

- 3 foot, semi-rigid snake is easier to control
- Self-contained LED lighting
- Water proof connections

**CC2-CAM6F****6' x 10.2mm Camera**

6' snake with 10.2mm camera head for CobraCam2



- Standard 6 foot, semi-rigid snake for added reach
- Self-contained LED lighting
- Water proof connections

CC2-CAM10F**10' x 10.2mm Camera**

10' snake with 10.2mm camera head for CobraCam2

- 10 foot, semi-rigid snake for extended reach
- Self-contained LED lighting
- Water proof connections



CC2-XC3F
3' Extension Cable

Extend the usefulness of your CobraCam2



- Cable extension adds a longer reach to your existing CobraCam2 camera
- Combine cables to extend up to 100'
- Water proof connections

CC2-XC6F
6' Extension Cable

Extend the usefulness of your CobraCam2

- Cable extension adds a longer reach to your existing CobraCam2 camera
- Combine cables to extend up to 100'
- Water proof connections


CC2-XC10F
10' Extension Cable

Extend the usefulness of your CobraCam2

- Cable extension adds a longer reach to your existing CobraCam2 camera
- Combine cables to extend up to 100'
- Water proof connections


1101
1101-B Digital MultiMeter

Compact DMM with Backlit display and Temperature test

- 3 1/2 digit backlit display
- 20 Ranges & Functions: AC/DC Voltage, DC Current to 10A, Resistance, and Continuity
- Shock absorbing case with stand




2030
2030-C Pocket Sized DMM
Auto-ranging Pocket Sized DMM

- 37 Ranges and Functions: AC/DC Voltage to 600V, Current, Resistance, Capacitance and Frequency ranges
- Convenient compartment holds test leads securely
- Closing the cover ensures the unit is off, Preserving battery life

9007
9007 Digital MultiMeter
**Huge 1.4" Backlit display DMM
w/capacitance**

- 3 1/2 digit backlit display
- 31 ranges including: Voltage, Current to 20A, Resistance, and Continuity
- Shock absorbing, overmolded case w/ stand


9045
9045
**True RMS DMM with
Temperature, Capacitance, and Frequency**

- 6000 count auto ranging True RMS DMM
- AC/DC Voltage & Current, Resistance ranges
- Backlit display with 61 segment bargraph
- Shock absorbing, overmolded case w/stand


9055
6-in-1 EnviroMeter
Autorangeing DMM with multiple Environmental functions

- Built-in Light (Lux) and Sound Level (dB)
- Built-in Temperature and Relative Humidity
- Non-contact AC Voltage Detector
- 4000 count, fully annunciated, backlit display
- Shock absorbing, overmolded case w/ stand




TSC-MC1
SoniChek MC

Mini Sound Level Meter

- C weighted reads 40-130dB from 31.5Hz-8KHz
- Measure sound level for PA, Home Theater, Alarm, Sound Systems, etc.
- Also features Min/Max and backlit display

3279
CableRater

dB Loss Measurement System

- Measure dB loss through passive and active components
- Verify installation before cable TV service is connected
- Test cables, splitters, amplifiers, etc.


3375
Fox Jr. & Hound Jr.

Compact Wire and Cable Tracing Kit

- The compact design allows you to Identify, Locate and Trace wires inside tight locations
- Adjustable warble tone
- RJ-11/RJ-45 and Alligator Clip connections


3388
HotWire Fox & Hound

Live Wire Circuit Tracing Kit

- Identify, Locate, and Trace Energized wires from 1V to 220V
- Trace wires up to 1000 feet in length
- Locates wires up to 3 feet away in open air
- Includes modular leads & hard-sided carrying case




3399
Fox 2 & Hound 3 Kit
Deluxe Wire & Cable Tracing Kit

- Identify, Locate, and Trace wires inside wall bays and wire runs with TrueTrace technology
- Use in houses, factories, boating, and more

9601
Sniff-It 2
Non-Contact AC Voltage Detector with Adjustable Sensitivity

- Detects from 5-600 Volts AC
- Pocket sized for convenience
- Light and Tone vary with proximity to voltage


3274
WireMaster Coax
8-Way Coaxial Cable Mapper

- ID up to 8 cables with included BNC remotes
- Test for Opens, Shorts, & Overvoltage
- A must for CCTV, Security, and Surveillance System Installers


3281
WireMaster Mapper
8-Way Wire & Cable Mapping Kit

- Quickly map all types of cables using the included 39 remotes and adapters
- Includes 8 each: BNC, F, RJ-11/RJ-45, and Alligator Clip Remotes plus Carrying Case




9615
Line-Bug 4

Phone / LAN Jack tester

- Test for phone line connection and polarity
- RJ-11 or RJ-45 interface
- Protect your expensive LAN tester from damaging telephone current

9650
Breaker Sniff-It

Digital Circuit Breaker Identifier

- Positively identifies circuit breakers without making adjustments
- Micro-processor controlled reduces false readings
- 90-280 VAC operation


3240
PairMaster

LAN Cable Test Set w/2 Remotes

- Test and map Cat 5 or Cat 6 cables with the press of a button
- Test for 8 Faults: Open, Short, Crossed, Split, Reversed, Transposed, Overvoltage, Double Split (NEXT)


3241
PairMaster Kit

 LAN Cable Cable Testing Kit
 w/16 Remotes and Carrying Case

- Test and map Cat 5 or Cat 6 cables with the press of a button
- Test for 8 Faults: Open, Short, Crossed, Split, Reversed, Transposed, Overvoltage, Double Split (NEXT)




3256
WireMaster HDMI-2
High Definition Cable Tester

- Tests HDMI cables including v1.4
- Automatic and Manual test modes
- Lightweight and easy to use
- Carrying case included

3254
WireMaster XR-2
LAN Cable Test Set with Tone Generator

- Test installed LAN cables or patch cables
- RJ-11 & RJ-45 connections
- Generates tracer tone


3260
WireMaster XR-5
5 Cable Test Set

- Test 5 wire types: RJ-11, RJ-45, BNC, Firewire, and USB
- Test installed wiring or patch cables
- Simple one button test confirms good cable or identifies faults


3271
TDR Cable Fault Finder
**Digital Cable Length Meter
& Tone Generator**

- Easily find distance to fault or cable length from one end
- Test all types of communication cables
- 39 standard cable presets or manual selection




9200
Model 9200-A
Mini AC Clamp-on meter

- Measure AC Amps from 0-300 amps
- Sensitive 20A range w/ 0.01 amp resolution
- Data Hold Function
- Carrying case included

9310
Model 9310-A
**AC/DC Clamp-on Meter
w/Temp, Cap, Freq and Backlit display**

- Measure AC/DC Current to 1000A
- Auto Ranging DMM measurements include: AC/DC Voltage, Capacitance, Resistance, Diode, Frequency and Temperature
- Data Hold and Relative functions


9320
Model 9320-A
**True RMS AC/DC Clamp-on Meter
w/Temp, Cap, Freq and Backlit display**

- Measure AC/DC Current to 1000A
- Auto Ranging DMM measurements include: AC/DC Voltage, Capacitance, Resistance, Diode, Frequency and Temperature
- Data Hold and Relative functions

79-812
ModuLead
Premium Modular Test Leads

- Universal Design Fits Most Digital Multimeters
- UL Listed Premium Silicone Jacketed Wire with Banana Plugs
- Includes: 2 Pointed Probes, 2 Flat Probes, 2 Alligator Clips, 2 24" Leads, 2 60" Leads, Tri-Fold Carrying Case
- Lifetime Limited Warranty




3018
Model 310
Analog Hand Sized VOM

- VOM w/18 Ranges and Functions

Also Available:

- 3022 – 310C: Analog VOM w/18 Ranges and polarity reversing switch for DC ranges
- 3067 – 310-Tel: Analog VOM w/16 Ranges and polarity reversing switch for DC ranges

3145
Model 60
Ruggedized VOM – 28 Ranges

- 3 fuse design for a high level of protection
- 6" Mirrored scale reduces parallax error
- Confidence test to check batteries, fuses, leads, and meter accuracy
- High Impact Ruggedized case


3030
Model 630
Classic VOM – 25 Ranges

- Fuse and Diode overload protection
- 6" Mirrored scale reduces parallax error
- Decibel Scale for Audio
- AC/DC Volts, Resistance and DCmA

2010
Model 2000
Railroad Test Set

Measures AC/DC Voltage & Current, Resistance, Code Parameters, and Relay Contact On Time

Also Available:

- 2011 – 2001: w/100HZ and 250HZ cab filters
- 2012 – 2002: w/100HZ and 200HZ cab filters
- 2013 – 2003: w/60HZ and 250HZ cab filters





TRIPLETT

Test Equipment & Tools

100+ Years of Quality and Commitment



WWW.TRIPLETT.COM
1-800-TRIPLETT

Triplett Test Equipment & Tools

850 Perimeter Rd

Manchester, NH 03103

