

# Hubbell Floor Boxes

Featuring Hubbell SystemOne Floor Boxes

# HUBBELL



SystemOne 4x4



SystemOne Multimedia



Traditional Recessed



Traditional Flush



*Nobody delivers like Hubbell Commercial Solutions*



# Hubbell Floor Boxes

Featuring the unique capabilities of Hubbell's SystemOne universal cover and sub-plate design, Hubbell has expanded its floor box offering to provide industry leading flexibility while accommodating an extensive range of applications. Hubbell SystemOne is constructed to give customers the ability to create personal solutions for their most demanding, power, data and audio/video requirements. In addition, Hubbell continues to offer a complete variety of traditional flush and recessed floor box options.

Whatever your requirement, Hubbell has a solution. Combined with Hubbell SystemOne fire-rated poke-through products that offer the same unique advantages, Hubbell's entire delivery system package is second to none in providing a consistent aesthetic and functional solution for your power, data and audio/video needs.




## Hubbell SystemOne Floor Box applications...



### Multi-Service Applications

This Hubbell SystemOne sub-plate incorporates 2 standard Style Line® rectangular openings. These can be used for a variety of power and/or data applications. It will accommodate 15 or 20 amp, standard, isolated ground, GFCI or surge protected receptacles. Using communication frames it can provide up to a 6-port multi-service or a 12-port all communication solution.



### Multimedia Applications


Other Hubbell SystemOne sub-plates are designed to meet the growing needs of the audio and video markets. Some sub-plates provide power outlets with Hubbell's audio/video products including 15-Pin SVGA, RCA, S-Video, 3.5mm stereo, and XLR microphone jacks. Another sub-plate can accommodate Extron® Electronics's MAAP and AAP series audio/video modules.



### 4X4 Applications

Provides maximum power capacity for flush, multi-service applications. This sub-plate features a pre-wired four outlet 20A, 125V receptacle and four openings for snap-in flush mount Hubbell modular jacks and audio/video snap-in connectors.






#### Advantage

- **Best in Class Products**  
Easily upgraded as user's needs change.
- **Ease of Installation**  
Modular sub-plate design facilitates quick and efficient moves, adds and changes.
- **Application Solutions**  
Highest capacity and widest variety of power, data and audio/video solutions.

### Traditional Floor Boxes...




#### Flush Applications

Hubbell offers a wide variety of traditional solutions including single and multi-gang cast iron, stamped steel and non-metallic floor boxes in both round and rectangular designs. These boxes can be finished with either brushed brass or aluminum covers and flanges to match any office décor. All Hubbell floor box assemblies exceed UL 514A scrub water exclusion requirements.



#### Recessed Applications

For applications where recessed connections are desired, Hubbell has a complete line of recessed stamped steel and cast iron floor boxes, from two to eight gangs. A variety of modular face plates are available to meet a wide array of power, data, voice and audio/video requirements. Carpet and tile cover/flange assemblies are offered in painted brass, aluminum, black, gray, brown and ivory colors.



#### Wooden Floor Applications

Hubbell offers round, single service and rectangular, multi-service floor boxes for wooden floor applications. The rectangular boxes are available in one, two and three-gang options and feature removable barriers for maximum capacity while maintaining separation of power and low voltage. A variety of covers and flanges are available in brushed aluminum or brass to meet aesthetic requirements.

## Hubbell SystemOne Non-Metallic Floor Box




Saves time and money on installation with a simple saw cut after pour adjustment.

Oversized 1 1/2" data conduit hub provides for increased cable capacity and helps maintain proper bend radius suitable for Category 6/6a, 5e, coax and fiber cables.

Parallel conduit hubs reduce labor and material costs and facilitate easier wire pulling in dual-service applications.

- Provides an economical, easy to install in-floor delivery system for large, open plan spaces.
- Accepts all Hubbell SystemOne universal covers and sub-plates for both single and dual service applications.
- Convenient cubic inch capacity markings on inside allow for easy inspection.
- Corresponding graduated cubic inch markings on dividers.
- High-strength rigid PVC construction that is non-corrosive.
- Supplied with concrete cap, conduit reducers, and conduit hub plugs.

## Hubbell SystemOne Universal Cover



Hinged doors open 180 degrees flush to the carpet flange or tile.

Screws allow each door to be secured independently.

Universal carpet or tile flange can be used for Hubbell SystemOne Fire-Rated Poke-Through or PVC Floor Box.

- Cast aluminum construction available in durable black, gray, brass, aluminum and ivory powder coat finishes.
- Features ScrubShield™ technology that exceeds UL514A and UL514C scrub water exclusion requirements.
- Provides consistent look and maximum functionality throughout the installed life.

## Hubbell SystemOne Sub-Plates

While no one can predict the future, Hubbell's modular sub-plate design allows users to economically upgrade Hubbell SystemOne Floor Boxes to accommodate future moves, adds and changes.



- Hubbell 4X4: four 20A, 125V receptacles, four openings for voice/data jacks and multimedia connectors.
- Hubbell INFINESTATION™ front loading modular connectivity.
- Accommodates Extron® Electronic's Architectural Series audio/video system integration products.
- Ortronics®, Siemon™, Panduit®, SYSTIMAX® and keystone options enable maximum data flexibility.
- Large capacity and multi-service furniture feed applications.
- Accommodates GFCI, surge and standard Style Line® receptacles.
- Twist-Lock® receptacle with or without jack openings.









# Hubbell SystemOne Non-Metallic Floor Box

|                                                                                                                                                                                                                                               |                                                                                   |                                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                             |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>S1PFB</b><br><b>Round Multi-Service PVC Floor Box</b><br>Features (2) 1 1/2" hubs for low voltage and (2) 1" hubs for power. Includes concrete cover and a variety of reducers and closure plugs that allow a full range of conduit sizes. |  | Min. Depth of Pour<br><br>Capacity<br><br>Diameter (External)<br>Diameter (Internal)<br>Height<br>Hubs<br>Conduit Selection | Ranges from 3" to 5" depending on application. See sub-plates below for details.<br>100 cubic inches prior to cutting level to floor (19.5 cubic inches per inch of depth).<br>5.75"<br>5.00"<br>6.00"<br>(2) 1 1/2" and (2) 1" conduit hubs<br>Accepts 3/4", 1", 1 1/4", 1 1/2" schedule 40 and schedule 80 rigid PVC conduit and E.N.T. (electrical non-metallic tubing). |
| <b>S1DIV1</b><br><b>Side by Side Divider</b><br>Required for use with catalog number S1SP (Style Line®/GFCI) sub-plate when used in multi-service applications. All other sub-plates include the appropriate dividers.                        |  |                                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                             |

## Hubbell SystemOne Universal Covers

|                                                                                                                                                                                                                                                                                                     |                                                                                                                                                                                                                                                                                                     |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Universal, Cast Aluminum Carpet Flange &amp; Cover Assembly</b><br>Catalog Number<br><b>S1CFCBRS</b> Brass<br><b>S1CFCAL</b> Aluminum<br><b>S1CFCBL</b> Black<br><b>S1CFCGY</b> Gray<br><b>S1CFCI</b> Ivory<br> | <b>Universal, Cast Aluminum Tile Flange &amp; Cover Assembly</b><br>Catalog Number<br><b>S1TFCBRS</b> Brass<br><b>S1TFCAL</b> Aluminum<br><b>S1TFCBL</b> Black<br><b>S1TFCGY</b> Gray<br><b>S1TFCI</b> Ivory<br> |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Sub-Plates

|                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                                                |                                                                                                                                                                                                                                                                                                                                                                                 |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>S1SP</b> <b>Style Line/GFCI</b><br>(2) Style Line openings for power and/or datacom applications.<br>                                                                                        | <b>S1SP4X4</b> <b>Hubbell 4 X 4</b><br>(4) 20A, 125V receptacles.<br>(4) Keystone openings for Hubbell jacks or flush A/V connectors.<br>                                                   | <b>S1SPTL</b> <b>Twist-Lock® + Data</b><br>20 or 30 Amp TL rec. (1.56" OD).<br>(2) Keystone openings for Hubbell jacks or flush A/V connectors.<br>                                                                                                                                         |
| <b>S1SP4IM</b> <b>Hubbell Datacom</b><br>1 unit flush INFIneSTATION™ opening. 3 unit recessed INFIneSTATION opening for data, voice, and A/V applications.<br>(See back cover for details)<br> | <b>S1SP3IM</b> <b>Hubbell A/V + Power</b><br>(1) 20A, 125V receptacle.<br>3 unit recessed INFIneSTATION opening for data, voice, and A/V applications.<br>(See back cover for details)<br> | <b>S1SPFFBRS</b> Brass <b>Furniture</b><br><b>S1SPFFAL</b> Alum. <b>Feed Cover/</b><br><b>S1SPFFBL</b> Black <b>Flange</b><br><b>S1SPFFGY</b> Gray<br>(1) 3/4" & (1) 1 1/2" KOs for power and/or datacom applications.<br><b>Universal Cover not required. Includes carpet flange.</b><br> |
| <b>S1SPEXT1</b> <b>Extron® MAAP + Power</b><br>(1) 20A, 125V receptacle.<br>Recessed opening for (3) single Extron MAAP Series adapter plates.<br>                                             | <b>S1SPEXT2</b> <b>Extron AAP + Power</b><br>(1) 20A, 125V receptacle.<br>Recessed opening for (1) single Extron MAAP and (2) single AAP Series adapter plates.<br>                        | <b>S1SPEXT3</b> <b>Extron Datacom</b><br>Recessed opening for (2) single Extron MAAP and (2) single AAP Series adapter plates.<br>                                                                                                                                                         |
| <b>S1SPORT</b> <b>Ortronics Series II® + Power</b><br>(1) 20A, 125V receptacle.<br>Recessed opening for (3) 1 unit Ortronics Series II modules.<br>                                            | <b>S1SPTRAC</b> <b>Ortronics TracJack® + Power</b><br>(1) 20A, 125V receptacle.<br>Recessed bezel for (6) Ortronics TracJack modules.<br>                                                  | <b>S1SPMAX</b> <b>Siemon MAX® + Power</b><br>(1) 20A, 125V receptacle.<br>Recessed bezel for (6) Siemon MAX modules.<br>                                                                                                                                                                   |
| <b>S1SP4X4PA</b> <b>Panduit Mini-Com® 4 X 4</b><br>(4) 20A, 125V receptacles<br>(4) Openings for Panduit Mini-Com Connectivity.<br>                                                            | <b>S1SP4X4SYS</b> <b>SYSTIMAX® 4 X 4</b><br>(4) 20A, 125V receptacles.<br>(4) Openings for SYSTIMAX Connectivity.<br>                                                                      |                                                                                                                                                                                                                                                                                                                                                                                 |

 Signifies minimum depth of concrete pour in inches for Hubbell SystemOne S1PFB Floor Box.



## Flush Round Single or Multi-Service Non-Metallic Floor Box

Catalog Number

### PFB1 Round Single or Low Capacity Multi-Service PVC Floor Box

Features (2) 1" and (2) 3/4" conduit hubs. Includes concrete cover and four dual purpose reducer/closure plugs. (2) 1" plugs close off 1" hub or reduce 1" to 3/4". (2) 3/4" plugs close off 3/4" hub or reduce 3/4" to 1/2".



Min. Depth of Pour Capacity

Diameter (External)  
Diameter (Internal)  
Height  
Hubs  
Conduit Selection

3.00"  
100 cubic inches prior to cutting level to floor (19.5 cubic inches per inch of depth).  
5.75"  
5.00"  
6.00"  
(2) 1" and (2) 3/4" conduit hubs  
Accepts 1/2", 3/4", 1" schedule 40 and schedule 80 rigid PVC conduit and E.N.T. (electrical non-metallic tubing). Use catalog number PFBYA1 3/4" "Y" adapter to feed parallel runs of 3/4" conduit.

### PFBA1A Adapter

Required for all applications.



### PFBT1A Low Voltage Divider

Required for use with catalog number PFB1 when used in multi-service applications. Accepts Hubbell standard duplex receptacles or 15A Twist-Lock duplex receptacles (HBL4700 series).



### PFBYA1 "Y" Adapter

3/4" "Y" adapter to feed parallel runs of 3/4" conduit.

## Flush Round Floor Box Covers and Flanges

### Multi-Service Cover and Flange Assemblies

Includes floor box cover with duplex flaps, (2) 1/2" dia. low voltage feed through holes and matching carpet flange.

SF39253A



Brass

PFBCBRA



Brown Plastic

PFBCIA



Ivory Plastic

PFBCGYA



Gray Plastic

PFBCBKA



Black Plastic

### Single Service Covers

Brass  
Aluminum

S3925  
SA3925



Duplex  
Flap

S3725  
SA3725



Duplex  
Screw

S2525  
SA2525



2 1/8" x 3/4"  
Combination

S2725  
SA2725



2 1/8" x 1"  
Combination

S2925  
SA2925



2 1/8" Single  
Receptacle

S3525  
SA3525



2 3/8" Single  
Receptacle

S3325  
—



2 1/8" Single  
Receptacle  
(Terrazzo Floor)

### Metal Carpet Flange

Use with single service covers for carpet applications.

S3082



Brass

### Adapter Ring

Use with single service covers for tile applications.

S5016



Brass

SA5016



Aluminum

### Furniture Feed Plate

PFBP1



Steel

### One Piece Cover and Carpet Flange

Brass

SF3925\*



Duplex  
Flap

SF2525\*



2 1/8" x 3/4"  
Combination

SF2725\*



2 1/8" x 1"  
Combination


SF2925\*



2 1/8" Single  
Receptacle

\* Catalog number S5016 adapter ring is required for mounting SF series covers onto PFBA1A.

## Flush Round Single Service Floor Boxes

| Box Material                                                                      |                                                                                   |         | Cast Iron                                                                         |          |                                                                                     | Stamped Steel                                                                       |                                                                                     |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|---------|-----------------------------------------------------------------------------------|----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| Collar Material                                                                   |                                                                                   |         |                                                                                   |          |                                                                                     |                                                                                     |                                                                                     |
| Brass                                                                             | B2536                                                                             | B253641 | B2506                                                                             | B2506415 | B2537                                                                               | B2527                                                                               | B2529                                                                               |
| Aluminum                                                                          | BA2536                                                                            | —       | —                                                                                 | —        | BA2537                                                                              | BA2527                                                                              | BA2529                                                                              |
|  |  |         |  |          |  |  |  |
| Min. Depth of Pour                                                                | 3.75"                                                                             | 3.75"   | 4.75"                                                                             | 4.75"    | 3.00"                                                                               | 4.00"                                                                               | 3.00"                                                                               |
| Adjustability<br>(Fully, Semi, Non)                                               | Fully                                                                             | Fully   | Fully                                                                             | Fully    | Fully                                                                               | Fully                                                                               | Fully                                                                               |
| Before Pour External<br>Height Adjustment                                         | 1.25"                                                                             | 1.25"   | —                                                                                 | —        | 1.25"                                                                               | 1.25"                                                                               | 1.25"                                                                               |
| After Pour Internal Height<br>Adjustment                                          | .38"                                                                              | .38"    | .63"                                                                              | .63"     | .38"                                                                                | .38"                                                                                | .38"                                                                                |
| Cubic Inch Capacity                                                               | 33.00                                                                             | 33.00   | 50.80                                                                             | 50.80    | 33.00                                                                               | 54.00                                                                               | 37.30                                                                               |
| Dimensions - A                                                                    | 4.19"                                                                             | 4.19"   | 4.19"                                                                             | 4.19"    | 4.19"                                                                               | 4.19"                                                                               | 4.19"                                                                               |
| Dimensions - B                                                                    | 3.09"                                                                             | 3.09"   | 4.75"                                                                             | 4.75"    | 2.81"                                                                               | 3.88"                                                                               | 2.91"                                                                               |
| Threaded Hub Sizes                                                                | (4) ¾"                                                                            | (4) 1"  | (4) 1 ¼"                                                                          | (4) 1 ½" | (4) ¾"                                                                              | —                                                                                   | —                                                                                   |
| Knockouts - Opposite Sides                                                        | —                                                                                 | —       | —                                                                                 | —        | —                                                                                   | (1) 1" & (1) ¾"                                                                     | (2) ½" & (1) ¾"                                                                     |
| Knockouts - Opposite Ends                                                         | —                                                                                 | —       | —                                                                                 | —        | —                                                                                   | (1) 1 ¼" & (1) ¾"                                                                   | (1) ½" & (1) ½"                                                                     |
| Knockouts - Bottom                                                                | —                                                                                 | —       | —                                                                                 | —        | —                                                                                   | (3) ½" & (2) ¾"                                                                     | (3) ½" & (2) ¾"                                                                     |

## Flush Round Single Service Floor Boxes

### Single Service Covers

|                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                       |                                                                                       |                                                                                       |       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------|
| Brass                                                                               | S3925                                                                               | S3725                                                                               | S2525                                                                               | S2725                                                                                 | S2925                                                                                 | S3525                                                                                 | S3325 |
| Aluminum                                                                            | SA3925                                                                              | SA3725                                                                              | SA2525                                                                              | SA2725                                                                                | SA2925                                                                                | SA3525                                                                                | —     |
|  |  |  |  |  |  |  |       |
| Duplex<br>Flap                                                                      | Duplex<br>Screw                                                                     | 2 1/8" x 3/4"<br>Combination                                                        | 2 1/8" x 1"<br>Combination                                                          | 2 1/8" Single<br>Receptacle                                                           | 2 3/8" Single<br>Receptacle                                                           | 2 1/8" Single<br>Receptacle<br>(Terrazzo Floor)                                       |       |


### Carpet Flanges

|                                                                                     |                                                                                     |                                                                                      |                                                                                       |                                  |       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|----------------------------------|-------|
| 5 1/4" Diameter                                                                     | S3182                                                                               | SA3182                                                                               | S3079                                                                                 | Carpet Flange<br>6 1/4" Diameter | S3082 |
|  |  |  |  |                                  |       |
| Brass                                                                               | Aluminum                                                                            | Clear Polycarbonate                                                                  | Brass                                                                                 |                                  |       |

### One Piece Cover and Carpet Flange

|                                                                                     |                                                                                     |                                                                                      |                                                                                       |        |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--------|
| Brass                                                                               | SF3925                                                                              | SF2525                                                                               | SF2725                                                                                | SF2925 |
|  |  |  |  |        |
| Duplex<br>Flap                                                                      | 2 1/8" x 3/4"<br>Combination                                                        | 2 1/8" x 1"<br>Combination                                                           | 2 1/8" Single<br>Receptacle                                                           |        |

## Flush Rectangular Non-Metallic Floor Boxes with Non-Metallic Covers

| Number of Gangs                                                                   | 1-Gang<br>PFBRG1                                                                  | 2-Gang<br>PFBRG2                                                                  | 3-Gang<br>PFBRG3                                                                    |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|  |  |  |  |
| Min. Depth of Pour                                                                | 3.00"                                                                             | 3.00"                                                                             | 3.00"                                                                               |
| Cubic in. Capacity per Gang                                                       | 14.3 per 1" depth                                                                 | 14.3 per 1" depth                                                                 | 14.3 per 1" depth                                                                   |
| Dimensions – A                                                                    | 3.60"                                                                             | 6.82"                                                                             | 10.04"                                                                              |
| Dimensions – B                                                                    | 5.44"                                                                             | 8.66"                                                                             | 11.87"                                                                              |
| Dimensions – C                                                                    | 5.42"                                                                             | 5.42"                                                                             | 5.42"                                                                               |
| Dimensions – D                                                                    | 6.90"                                                                             | 6.90"                                                                             | 6.90"                                                                               |
| Dimensions – E                                                                    | 6.00"                                                                             | 6.00"                                                                             | 6.00"                                                                               |
| Dimensions – F                                                                    | 4.88"                                                                             | 8.13"                                                                             | 11.35"                                                                              |
| Dimensions – G                                                                    | 6.00"                                                                             | 6.00"                                                                             | 6.00"                                                                               |
| Hubs                                                                              | (4) 1"                                                                            | (6) 1"                                                                            | (8) 1"                                                                              |
| Reducers/Plugs                                                                    | (4) 1" to 3/4"                                                                    | (6) 1" to 3/4"                                                                    | (8) 1" to 3/4"                                                                      |


## Flush Rectangular Non-Metallic Covers and Flanges

### Required Components for Carpet Applications

Carpet Flanges – Gray

| No. of Gangs | 1-Gang<br>PFBFRGY1                                                                  | 2-Gang<br>PFBFRGY2                                                                  | 3-Gang<br>PFBFRGY3                                                                   |
|--------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
|              |  |  |  |

Cover with Duplex and Style Line®  
Inserts - Gray  
One Required per Gang  
**PFBR826GYA**




### Required Components for Tile Applications

|                                        |                                         |
|----------------------------------------|-----------------------------------------|
| Mounting Collar                        | Cover Frame                             |
| One Required per Gang<br><b>PFBRMC</b> | One Required per Gang<br><b>PFBFRFA</b> |



Cover with Duplex and Style Line®  
Inserts - Gray  
One Required per Gang  
**PFBR826GYA**






## Flush Rectangular Non-Metallic Floor Boxes with Metal Covers

Number of Gangs

1-Gang  
PFBRG1

2-Gang  
PFBRG2

3-Gang  
PFBRG3



|                             |                   |                   |                   |
|-----------------------------|-------------------|-------------------|-------------------|
| Min. Depth of Pour          | 3.00"             | 3.00"             | 3.00"             |
| Cubic in. Capacity per Gang | 14.3 per 1" depth | 14.3 per 1" depth | 14.3 per 1" depth |
| Dimensions – A              | 3.60"             | 6.82"             | 10.04"            |
| Dimensions – B              | 5.44"             | 8.66"             | 11.87"            |
| Dimensions – C              | 5.42"             | 5.42"             | 5.42"             |
| Dimensions – D              | 6.90"             | 6.90"             | 6.90"             |
| Dimensions – E              | 6.00"             | 6.00"             | 6.00"             |
| Dimensions – F              | 4.88"             | 8.13"             | 11.35"            |
| Dimensions – G              | 6.00"             | 6.00"             | 6.00"             |
| Hubs                        | (4) 1"            | (6) 1"            | (8) 1"            |
| Reducers/Plugs              | (4) 1" to 3/4"    | (6) 1" to 3/4"    | (8) 1" to 3/4"    |

## Flush Rectangular Metal Covers and Flanges

### Required Components for Carpet and Tile Applications

Adapter Frame and Grounding Lug – One Required per Gang

Brass  
Aluminum

S5017G  
SA5017G



Adapter Collar – Gray  
One Required per Gang  
PFBRAC



### Covers – One Required per Gang

|          |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                       |                                                                                       |                                                                                       |
|----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| Brass    | S3825                                                                               | S3625                                                                               | S3826                                                                               | S2425                                                                               | S2625                                                                                 | S2825                                                                                 | S3813                                                                                 |
| Aluminum | SA3825                                                                              | SA3625                                                                              | SA3826                                                                              | SA2425                                                                              | SA2625                                                                                | —                                                                                     | SA3813                                                                                |
|          |  |  |  |  |  |  |  |
|          | Duplex<br>Flap                                                                      | Duplex<br>Screw                                                                     | Style Line<br>Opening                                                               | 2 1/8" x 3/4"<br>Combination                                                        | 2 1/8" x 1"<br>Combination                                                            | 2 1/8" Single<br>Receptacle                                                           | Blank                                                                                 |

### Carpet Flanges (Not Required for Tile Applications)

#### Tapered Flange

No. of Gangs

Brass

Aluminum


1-Gang  
SB3083  
SA3083

2-Gang  
SB3084  
SA3084

3-Gang  
SB3085  
SA3085



## Flush Rectangular Cast Iron Floor Boxes

| Box Material                                                                     |                                                                                   |         | Cast Iron                                                                         |                      |                                                                                   |                                  |                                                                                    |                                                                                     |                                                                                     |
|----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|---------|-----------------------------------------------------------------------------------|----------------------|-----------------------------------------------------------------------------------|----------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| Collar Material                                                                  |                                                                                   |         |                                                                                   |                      |                                                                                   |                                  |                                                                                    |                                                                                     |                                                                                     |
| Brass                                                                            | B2436                                                                             | B243641 | B4233                                                                             | B423341              | B4333                                                                             | B433361                          | B2414                                                                              | B4214                                                                               | B4314                                                                               |
| Aluminum                                                                         | BA2436                                                                            | —       | BA4233                                                                            | —                    | BA4333                                                                            | —                                | —                                                                                  | —                                                                                   | —                                                                                   |
|  |  |         |  |                      |  |                                  |  |  |  |
| Min. Depth of Pour                                                               | 3.75"                                                                             | 3.75"   | 3.75"                                                                             | 3.75"                | 3.75"                                                                             | 3.75"                            | 2.00"                                                                              | 2.00"                                                                               | 2.00"                                                                               |
| Adjustability<br>(Fully, Semi, Non)                                              | Fully                                                                             | Fully   | Fully                                                                             | Fully                | Fully                                                                             | Fully                            | Semi                                                                               | Semi                                                                                | Semi                                                                                |
| Before Pour External<br>Height Adjustment                                        | 1.25"                                                                             | 1.25"   | 1.25"                                                                             | 1.25"                | 1.25"                                                                             | 1.25"                            | 1.25"                                                                              | 1.25"                                                                               | 1.25"                                                                               |
| After Pour Internal<br>Height Adjustment                                         | .38"                                                                              | .38"    | .63"                                                                              | .63"                 | .63"                                                                              | .63"                             | —                                                                                  | —                                                                                   | —                                                                                   |
| Cubic Inch Capacity                                                              | 33.00                                                                             | 33.00   | 36.50<br>Per<br>Gang                                                              | 36.50<br>Per<br>Gang | 34.80<br>Middle<br>36.50<br>Ends                                                  | 34.80<br>Middle<br>36.50<br>Ends | 16.00                                                                              | 16.00<br>Per<br>Gang                                                                | 16.00<br>Per<br>Gang                                                                |
| Dimensions – A                                                                   | 4.38"                                                                             | 4.38"   | 4.38"                                                                             | 4.38"                | 4.38"                                                                             | 4.38"                            | 4.38"                                                                              | 4.38"                                                                               | 4.38"                                                                               |
| Dimensions - B                                                                   | 3.19"                                                                             | 3.19"   | 3.44"                                                                             | 3.44"                | 3.44"                                                                             | 3.44"                            | 2.00"                                                                              | 2.00"                                                                               | 2.00"                                                                               |
| Dimensions - C                                                                   | 3.19"                                                                             | 3.19"   | 6.38"                                                                             | 6.38"                | 9.56"                                                                             | 9.56"                            | 3.19"                                                                              | 6.38"                                                                               | 9.56"                                                                               |
| Threaded Hub Sizes                                                               | (4) ¾"                                                                            | (4) 1"  | (6) ¾"                                                                            | (4) 1" &<br>(2) ¾"   | (8) ¾"                                                                            | (6) 1" &<br>(2) ¾"               | (2) ¾"                                                                             | (4) ¾"                                                                              | (6) ¾"                                                                              |

## Flush Rectangular Floor Box Covers and Flanges


### Covers

|          | S3825                                                                               | S3625                                                                               | S3826                                                                               | S2425                                                                               | S2625                                                                               | S2825                                                                                 | S3425                                                                                 | S3813                                                                                 |
|----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| Brass    | SA3825                                                                              | SA3625                                                                              | SA3826                                                                              | SA2425                                                                              | SA2625                                                                              | —                                                                                     | —                                                                                     | SA3813                                                                                |
| Aluminum |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                       |                                                                                       |                                                                                       |
|          |  |  |  |  |  |  |  |  |
|          | Duplex<br>Flap                                                                      | Duplex<br>Screw                                                                     | Style Line<br>Opening                                                               | 2 1/8" x 3/4"<br>Combination                                                        | 2 1/8" x 1"<br>Combination                                                          | 2 1/8" Single<br>Receptacle                                                           | 2 3/8" Single<br>Receptacle                                                           | Blank                                                                                 |

### Carpet Flanges

|                     | 1-Gang                                                                              | 2-Gang                                                                              | 3-Gang                                                                                |
|---------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| Brass               | SB3083                                                                              | SB3084                                                                              | SB3085                                                                                |
| Aluminum            | SA3083                                                                              | SA3084                                                                              | SA3085                                                                                |
| Clear Polycarbonate | S3083                                                                               | S3084                                                                               | S3085                                                                                 |
|                     |  |  |  |

## Flush Rectangular Stamped Steel Floor Boxes

| Box Material                                                                      |                                                                                   | Stamped Steel                                                                     |                                                                                   |                                                                                    |                                                                                     |                                                                                     |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| Collar Material                                                                   |                                                                                   |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |
| Brass                                                                             | B2431                                                                             | B2432                                                                             | B2433                                                                             | B2421                                                                              | B2422                                                                               | B2423                                                                               |
| Aluminum                                                                          | BA2431                                                                            | BA2432                                                                            | BA2433                                                                            | BA2421                                                                             | BA2422                                                                              | BA2423                                                                              |
|  |  |  |  |  |  |  |
| Min. Depth of Pour                                                                | 3.75"                                                                             | 3.75"                                                                             | 3.75"                                                                             | 2.75"                                                                              | 2.75"                                                                               | 2.75"                                                                               |
| Adjustability<br>(Fully, Semi, Non)                                               | Fully                                                                             | Fully                                                                             | Fully                                                                             | Fully                                                                              | Fully                                                                               | Fully                                                                               |
| Before Pour External<br>Height Adjustment                                         | 1.25"                                                                             | 1.25"                                                                             | 1.25"                                                                             | 1.25"                                                                              | 1.25"                                                                               | 1.25"                                                                               |
| After Pour Internal<br>Height Adjustment                                          | .50"                                                                              | .50"                                                                              | .50"                                                                              | .50"                                                                               | .50"                                                                                | .50"                                                                                |
| Cubic Inch Capacity                                                               | 60.00                                                                             | 52.80<br>Per Gang                                                                 | 50.80<br>Per Gang                                                                 | 39.50                                                                              | 35.00<br>Per Gang                                                                   | 34.00<br>Per Gang                                                                   |
| Dimensions – A                                                                    | 4.38"                                                                             | 4.38"                                                                             | 4.38"                                                                             | 4.38"                                                                              | 4.38"                                                                               | 4.38"                                                                               |
| Dimensions - B                                                                    | 3.72"                                                                             | 3.72"                                                                             | 3.72"                                                                             | 2.74"                                                                              | 2.74"                                                                               | 2.74"                                                                               |
| Dimensions - C                                                                    | 3.19"                                                                             | 6.44"                                                                             | 9.67"                                                                             | 3.19"                                                                              | 6.44"                                                                               | 9.67"                                                                               |
| Knockouts -<br>Opposite Sides                                                     | (1) Concentric<br>¾", 1", 1 ¼"                                                    | (2) Concentric<br>¾", 1", 1 ¼"                                                    | (3) Concentric<br>¾", 1", 1 ¼"                                                    | (2) ½",<br>(1) ¾"                                                                  | (4) Concentric<br>½", ¾"                                                            | (6) Concentric<br>½", ¾"                                                            |
| Knockouts -<br>Opposite Ends                                                      | (1) Concentric<br>¾", 1", 1 ¼"                                                    | (1) Concentric<br>¾", 1", 1 ¼"                                                    | (1) Concentric<br>¾", 1", 1 ¼"                                                    | (1) ½",<br>(1) ¾"                                                                  | (2) Concentric<br>½", ¾"                                                            | (2) Concentric<br>½", ¾"                                                            |
| Knockouts -<br>Bottom                                                             | (2) Concentric<br>¾", 1", 1 ¼"                                                    | (4) Concentric<br>¾", 1", 1 ¼"                                                    | (6) Concentric<br>¾", 1", 1 ¼"                                                    | (2) Concentric<br>¾", 1", 1 ¼"                                                     | (4) Concentric<br>¾", 1", 1 ¼"                                                      | (6) Concentric<br>¾", 1", 1 ¼"                                                      |

## Flush Rectangular Floor Box Covers and Flanges

### Covers

|          | S3825                                                                               | S3625                                                                               | S3826                                                                               | S2425                                                                               | S2625                                                                                | S2825                                                                                 | S3425                                                                                 | S3813                                                                                 |
|----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| Brass    | SA3825                                                                              | SA3625                                                                              | SA3826                                                                              | SA2425                                                                              | SA2625                                                                               | —                                                                                     | —                                                                                     | SA3813                                                                                |
| Aluminum |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                      |                                                                                       |                                                                                       |                                                                                       |
|          |  |  |  |  |  |  |  |  |
|          | Duplex<br>Flap                                                                      | Duplex<br>Screw                                                                     | Style Line<br>Opening                                                               | 2 1/8" x 3/4"<br>Combination                                                        | 2 1/8" x 1"<br>Combination                                                           | 2 1/8" Single<br>Receptacle                                                           | 2 3/8" Single<br>Receptacle                                                           | Blank                                                                                 |

### Carpet Flanges

|                     | 1-Gang                                                                              | 2-Gang                                                                              | 3-Gang                                                                                |
|---------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| Brass               | SB3083                                                                              | SB3084                                                                              | SB3085                                                                                |
| Aluminum            | SA3083                                                                              | SA3084                                                                              | SA3085                                                                                |
| Clear Polycarbonate | S3083                                                                               | S3084                                                                               | S3085                                                                                 |
|                     |  |  |  |



## Recessed 4 and 8-Gang Floor Boxes

| Box Material                              | Stamped Steel                                                                     |                                                                                   |                                                                                    | Cast Iron                                                                           |
|-------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| Style                                     | 4-Gang Deep<br>HBLCFB301BASE                                                      | 4-Gang Shallow<br>HBLCFB401BASE                                                   | 8-Gang Deep<br>HBLCFB501BASE                                                       | 4-Gang Shallow<br>HBLCFB401CB                                                       |
|                                           |  |  |  |  |
| Min. Depth of Pour                        | 4.25"                                                                             | 3.00"                                                                             | 5.25"                                                                              | 3.25"                                                                               |
| Adjustability<br>(Fully, Semi, Non)       | Fully                                                                             | Fully                                                                             | Fully                                                                              | Fully                                                                               |
| Before Pour External<br>Height Adjustment | 1.50"                                                                             | 1.50"                                                                             | 1.50"                                                                              | 1.50"                                                                               |
| After Pour Internal<br>Height Adjustment  | .75"                                                                              | .75"                                                                              | .75"                                                                               | .75"                                                                                |
| Wiring Chambers                           | 4 (1 per gang)                                                                    | 4 (1 per gang)                                                                    | 4 (1 per 2 gangs)                                                                  | 4 (1 per gang)                                                                      |
| Cubic Inch Capacity                       | 29.50 per chamber                                                                 | 25.50 per chamber                                                                 | 49.50 per chamber                                                                  | 25.50 per chamber                                                                   |
| L x W x H                                 | 10.0" x 10.0" x 4.0"                                                              | 10.0" x 10.0" x 2.63"                                                             | 10.0" x 10.0" x 5.13"                                                              | 10.0" x 10.0" x 3.13"                                                               |
| Threaded Hubs / chamber                   | –                                                                                 | –                                                                                 | –                                                                                  | (2) 1"                                                                              |
| Knockouts<br>per chamber                  | (1) Concentric 1/2", 3/4"<br>(1) Concentric 3/4", 1"<br>(1) 1 1/4"                | (3) Concentric 1/2", 3/4"                                                         | (1) Concentric 1/2", 3/4"<br>(1) Concentric 3/4", 1"<br>(1) 1 1/4"                 | –                                                                                   |

## Recessed Floor Box Covers

### Steel Cover and Flange Assembly HBLTCGNTSW HBLTCGNTBKS



Granite



Black

## Face Plates

### HBLST302SGY



Duplex

### HBLDE301SGY



Style Line

### HBLTO310SGY



Toggle

### HBLTL318GY



Single Receptacle  
(1.39" Boss Dia.)

### HBLTL319SGY



Single Receptacle  
(1.56 Boss Dia.)

### HBLBL300SGY



Blank

### HBLIMFSGY



Hubbell  
INFINESTATION™

### HBL317SGY



Hubbell  
6-Port

### HBLAM303SGY



AMP-ACO

### HBLAMP313SGY



AMP 6-Port

### HBLKR314SGY



Krone®/Leviton®

### HBLLT309SGY



SYSTIMAX®

### HBLPA308SGY



Panduit  
Mini-Com®

### HBLNO309SGY



NORDX®  
6-Port

### HBLSI305SGY



Siemon  
CT® Series

### HBLSI315SGY



Siemon  
MAX® Series

### HBLOR306SGY



Ortronics  
Series II®

### HBLORT322SGY



Ortronics  
TracJack®

## Recessed 6-Gang Floor Boxes

### Stamped Steel

#### LCFBSSA



|                                           |                                       |
|-------------------------------------------|---------------------------------------|
| Min. Depth of Pour                        | 3.50"                                 |
| Adjustability<br>(Fully, Semi, Non)       | Fully                                 |
| Before Pour External<br>Height Adjustment | 1.25"                                 |
| Wiring Chambers                           | 6                                     |
| Cubic Inch Capacity<br>per Chamber        | (4) at 38.20<br>(2) at 25.40          |
| L x W x H                                 | 12.5" x 12.5" x 6.18"                 |
| Knockouts<br>per Chamber                  | (1) Concentric 1", 1 1/4"<br>(1) 3/4" |

### Cast Iron

#### LCFBCA



|                                           |                              |
|-------------------------------------------|------------------------------|
| Min. Depth of Pour                        | 3.65"                        |
| Adjustability<br>(Fully, Semi, Non)       | Fully                        |
| Before Pour External<br>Height Adjustment | 1.25"                        |
| Wiring Chambers                           | 6                            |
| Cubic Inch Capacity<br>per Chamber        | (4) at 36.80<br>(2) at 25.40 |
| L x W x H                                 | 13.0" x 13.0" x 6.35"        |
| Threaded Hub Sizes<br>per Chamber         | (1) 3/4"<br>(1) 1 1/4"       |

## Recessed Floor Box Covers – Carpet Applications

### Metallic Cover, Flange and Cable Doors

#### LCFBCBRSC



Brass Finish

#### LCFBCALC



Aluminum Finish

#### LCFBCGYC



Gray

#### LCFBCBKC



Black

### Reinforced Non-Metallic Cover, Flange and Cable Doors

#### LCFBCBRA



Brown

#### LCFBCGYA



Gray

#### LCFBCIA



Ivory

#### LCFBCBKA



Black

## Recessed Floor Box Covers – Tile Applications

### Metallic Cover and Cable Doors

#### LCFBCBRST




Brass Finish

#### LCFBCALT



Aluminum Finish

#### LCFBCGYT



Gray

#### LCFBCBKT



Black

## Face Plates

#### LCFBP8



Duplex  
Opening

#### LCGBP26



Style Line  
Opening

#### LCFBP720




Single Receptacle Opening  
(for 1.56" boss dia.)

#### LCFBP14



Blank

#### LCFBIM



3 Unit INFINESTATION™  
Opening (see back  
page for module options)

## Recessed 2-Gang Floor Boxes

### Stamped Steel

#### 3SFBSS



|                                           |                                    |
|-------------------------------------------|------------------------------------|
| Min. Depth of Pour                        | 3.00"                              |
| Adjustability<br>(Fully, Semi, Non)       | Fully                              |
| Before Pour External<br>Height Adjustment | 1.25"                              |
| After Pour Internal<br>Height Adjustment  | .44"                               |
| Wiring Chambers                           | 2                                  |
| Cubic Inch Capacity<br>per Chamber        | 22.40                              |
| L x W x H                                 | 12.25" x 5.50" x 2.88"             |
| Knockouts                                 |                                    |
| Opposite Ends                             | (1) 1"                             |
| Opposite Sides                            | (2) ¾"                             |
| Center Area                               | Concentric 1", 1 ¼"<br>(each side) |

### Cast Iron

#### 3SFBC



|                                           |                         |
|-------------------------------------------|-------------------------|
| Min. Depth of Pour                        | 3.00"                   |
| Adjustability<br>(Fully, Semi, Non)       | Fully                   |
| Before Pour External<br>Height Adjustment | 1.25"                   |
| After Pour Internal<br>Height Adjustment  | .44"                    |
| Wiring Chambers                           | 2                       |
| Cubic Inch Capacity<br>per Chamber        | 21.60                   |
| L x W x H                                 | 12.88" x 6.00" x 3.00"  |
| Threaded Hub Sizes                        |                         |
| Opposite Ends                             | (1) 1 ¼"                |
| Opposite Sides                            | (2) ¾"                  |
| Center Area                               | (1) 1 ¼"<br>(each side) |

## Recessed Floor Box Covers – Carpet Applications

### Reinforced Non-Metallic Cover, Flange and Cable Doors

#### 3SFBCBRA



Brown

#### 3SFBCIA



Ivory

#### 3SFBCGYA



Gray

#### 3SFBCBKA



Black

## Face Plates

#### 3SFBRP



Duplex  
Knockout

#### 3SFBDS



Style Line  
Opening

#### 3SFBS



Single Receptacle  
Opening (for  
1.39"  
boss dia.)

#### 3SFBB



Blank

#### 3SFBTP



Voice / Data  
2 - Jack Knockouts  
(.6" x .75")


#### 3SFBIM



3 unit  
INFINESTATION™  
Opening  
(see back page  
for module  
options)



## Flush Floor Boxes for Wooden Floors

| Box Material                                                                      | Rectangular Stamped Steel                                                         |                                                                                   |                                                                                    | Round Cast Iron                                                                     |                                                                                     |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| Collar Material                                                                   |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |
| Brass                                                                             | <b>B2481</b>                                                                      | <b>B2482</b>                                                                      | <b>B2483</b>                                                                       | <b>B2588</b>                                                                        | <b>B2588275</b>                                                                     |
| Aluminum                                                                          |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |
|  |  |  |  |  |  |
| Gangs                                                                             | Single                                                                            | Two                                                                               | Three                                                                              | Single                                                                              | Single                                                                              |
| Adjustability<br>(Fully, Semi, Non)                                               | Semi                                                                              | Semi                                                                              | Semi                                                                               | Non                                                                                 | Non                                                                                 |
| External Height<br>Adjustment                                                     | 1.00"                                                                             | 1.00"                                                                             | 1.00"                                                                              | -                                                                                   | -                                                                                   |
| Cubic Inch Capacity                                                               | 42.00                                                                             | 42.50 Per Gang                                                                    | 42.50 Per Gang                                                                     | 18.50                                                                               | 18.50                                                                               |
| Dimensions - A                                                                    | 4.50"                                                                             | 4.50"                                                                             | 4.50"                                                                              | 4.19"                                                                               | 4.19"                                                                               |
| Dimensions - B                                                                    | 3.13"                                                                             | 3.13"                                                                             | 3.13"                                                                              | 3.75"                                                                               | 3.75"                                                                               |
| Dimensions - C                                                                    | 3.20"                                                                             | 6.42"                                                                             | 9.64"                                                                              | -                                                                                   | -                                                                                   |
| Hubs/Knockouts -<br>Opposite Sides                                                | (1) Concentric<br>1/2", 3/4", 1"                                                  | (2) Concentric<br>1/2", 3/4", 1"                                                  | (3) Concentric<br>1/2", 3/4", 1"                                                   | -                                                                                   | (2) 3/4"                                                                            |
| Hubs/Knockouts -<br>Bottom                                                        | (1) Concentric<br>1/2" - 1 1/4"                                                   | (2) Concentric<br>1/2" - 1 1/4"                                                   | (3) Concentric<br>1/2" - 1 1/4"                                                    | (2) 1/2"                                                                            | (2) 1/2"                                                                            |

## Flush Floor Box Covers and Flanges

### Rectangular Covers

|          |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                      |                                                                                       |                                                                                       |                                                                                       |
|----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| Brass    | <b>S3825</b>                                                                        | <b>S3625</b>                                                                        | <b>S3826</b>                                                                        | <b>S2425</b>                                                                        | <b>S2625</b>                                                                         | <b>S2825</b>                                                                          | <b>S3425</b>                                                                          | <b>S3813</b>                                                                          |
| Aluminum | <b>SA3825</b>                                                                       | <b>SA3625</b>                                                                       | <b>SA3826</b>                                                                       | <b>SA2425</b>                                                                       | <b>SA2625</b>                                                                        | —                                                                                     | —                                                                                     | <b>SA3813</b>                                                                         |
|          |  |  |  |  |  |  |  |  |
|          | Duplex<br>Flap                                                                      | Duplex<br>Screw                                                                     | Style Line<br>Opening                                                               | 2 1/8" x 3/4"<br>Combination                                                        | 2 1/8" x 1"<br>Combination                                                           | 2 1/8" Single<br>Receptacle                                                           | 2 3/8" Single<br>Receptacle                                                           | Blank                                                                                 |

### Round Covers

|          |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                      |                                                                                       |                                                                                       |
|----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| Brass    | <b>S3925</b>                                                                        | <b>S3725</b>                                                                        | <b>S2525</b>                                                                        | <b>S2725</b>                                                                        | <b>S2925</b>                                                                        | <b>S3525</b>                                                                         | <b>S3325</b>                                                                          | <b>Round Flanges</b><br><b>S3082</b> (6 1/4" Dia.)<br><b>SA3182</b> (5 1/4" Dia.)     |
| Aluminum | <b>SA3925</b>                                                                       | <b>SA3725</b>                                                                       | <b>SA2525</b>                                                                       | <b>SA2725</b>                                                                       | <b>SA2925</b>                                                                       | <b>SA3525</b>                                                                        | —                                                                                     |                                                                                       |
|          |  |  |  |  |  |  |  |  |
|          | Duplex<br>Flap                                                                      | Duplex<br>Screw                                                                     | 2 1/8" x 3/4"<br>Comb.                                                              | 2 1/8" x 1"<br>Comb.                                                                | 2 1/8" Single<br>Receptacle                                                         | 2 3/8" Sin.<br>Receptacle                                                            | 2 1/8" Sin. Rec.<br>(Terrazzo Floor)                                                  |                                                                                       |


### Rectangular Flanges

|          |                                                                                     |                                                                                     |                                                                                     |
|----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| Brass    | <b>SB3083W</b>                                                                      | <b>SB3084W</b>                                                                      | <b>SB3085W</b>                                                                      |
| Aluminum | <b>SA3083W</b>                                                                      | <b>SA3084W</b>                                                                      | <b>SA3085W</b>                                                                      |
|          |  |  |  |
|          | 1-Gang                                                                              | 2-Gang                                                                              | 3-Gang                                                                              |

### One Piece Brass Cover and Carpet Flange

|                                                                                      |                                                                                       |                                                                                       |                                                                                       |
|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| <b>SF3925</b>                                                                        | <b>SF2525</b>                                                                         | <b>SF2725</b>                                                                         | <b>SF2925</b>                                                                         |
|  |  |  |  |
| Duplex<br>Flap                                                                       | 2 1/8" x 3/4"<br>Combination                                                          | 2 1/8" x 1"<br>Combination                                                            | 2 1/8" Single<br>Receptacle                                                           |

# Power, Data, Audio and Video Accessories

| Modular Jacks                                                                                                                                                                                                                                          | Multimedia Connectors                                                                                                                                        | INFIneSTATION® Modules<br>(Office White)                                                                                                          | Outlet Frames                                                                                                                                            | Wiring Devices                                                                                                                                                                    |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>HBL60W*</b><br>Category 6<br>Universal<br>Wired<br>Office White                                                                                                    | <b>SIFOW**</b><br>F-Type<br>F/F Coupler<br>Office White                     | <b>DFBM05OW</b><br>Blank<br>.5 Unit                              | <b>FCX244OW++</b><br>2-Port<br>Style Line®<br>Frame<br>Office White   | <b>HBL2152 +++</b><br>15A 125V<br>Style Line<br>Duplex<br>Receptacle<br>Brown                  |
| <b>HBL5EOW*</b><br>Category 5e<br>Universal<br>Wired<br>Office White                                                                                                  | <b>SIFGOW**</b><br>Gold F-Type<br>F/F Coupler<br>Office White               | <b>DFBM10W</b><br>Blank<br>1 Unit                                |                                                                                                                                                          |                                                                                                                                                                                   |
| <b>HBLUOW*</b><br>USOC<br>6-Position<br>Office White                                                                                                                  | <b>SIRCAxx***</b><br>RCA 110<br>Punch Down<br>Black                         | <b>DFBM15OW</b><br>Blank<br>1.5 Unit                             | <b>FCX344OW++</b><br>3-Port<br>Style Line<br>Frame<br>Office White    | <b>HBL2162 +++</b><br>20A 125V<br>Style Line<br>Duplex<br>Receptacle<br>Brown                  |
| <b>SIBOWPK10**</b><br>Blank<br>Module<br>Office White                                                                                                                 | <b>SIRCAFFxx +</b><br>Gold RCA<br>F/F Coupler<br>Pass-Thru<br>Office White  | <b>DF1KOW</b><br>1-Port<br>Keystone<br>Flat 1 Unit               |                                                                                                                                                          |                                                                                                                                                                                   |
| * Office White is standard color.<br>For other colors, replace<br>'OW' as follows:<br>BK = Black      B = Blue<br>EI = Electric Ivory    GY = Gray<br>GN = Green      OR = Orange<br>R = Red          TI = Telco Ivory<br>W = White        Y = Yellow. | <b>SIRCAFFxx +</b><br>Gold RCA<br>F/F Coupler<br>Pass-Thru<br>Office White  | <b>DF2KOW</b><br>2-Port<br>Keystone<br>Flat 1 Unit               |                                                                                                                                                          |                                                                                                                                                                                   |
| ** Office White is standard color.<br>For other colors, replace 'OW'<br>as follows:<br>GY = Gray      I = Ivory<br>W = White.                                                                                                                          | <b>SIRCASxx +</b><br>RCA Solder<br>Coupler<br>Office White                  | <b>DFA1KOW</b><br>1-Port<br>Keystone<br>Angled<br>1 Unit         | <b>FCX444OW++</b><br>4-Port<br>Style Line<br>Frame<br>Office White    | <b>HBL2310</b><br>20A 125V<br>Twist-Lock<br>Receptacle<br>(1.56" boss<br>diameter)<br>Black    |
| ***Housing color is Black.<br>Replace 'xx' with one of<br>the following to designate<br>insulator:<br>OW = Red      W = White<br>Y = Yellow                                                                                                            | <b>SISVFFBK</b><br>S-Video<br>F/F Coupler<br>Black                        | <b>DFA2KOW</b><br>2-Port<br>Keystone<br>Angled<br>1 Unit        |                                                                                                                                                          |                                                                                                                                                                                   |
| + Housing color is Black.<br>Replace 'xx' with one of<br>the following to designate<br>insulator:<br>R = Red      W = White<br>Y = Yellow    BK = Black                                                                                                | <b>SISVOW</b><br>S-Video<br>110 Coupler<br>Black                          | <b>DFA1SCOW</b><br>1 SC Duplex<br>Angled<br>1.5 Unit           | <b>FCX644OW++</b><br>6-Port<br>Style Line<br>Frame<br>Office White  | <b>HBL2320</b><br>20A 250V<br>Twist-Lock<br>Receptacle<br>(1.56" boss<br>diameter)<br>Black  |
| ++ Office White is standard<br>color. For other colors,<br>replace 'OW' as follows:<br>GY = Gray      I = Ivory<br>W = White      BK = Black                                                                                                           | <b>SIBNCOW**</b><br>BNC<br>Coupler<br>Office White                        | <b>DFA2SCOW</b><br>2 SC Duplex<br>Angled<br>1.5 Unit           |                                                                                                                                                          |                                                                                                                                                                                   |
| +++ Standard color is<br>Brown. For other colors, add<br>one of the following to the<br>end of the catalog number:<br>I = Ivory      GY = Gray<br>WA = White    BK = Black<br>OW = Office White                                                        | <b>SIFSCOW</b><br>SC Simplex<br>Adapter<br>Office White                   | <b>DFRA1KOW</b><br>1-Port<br>Keystone<br>Recessed<br>1.5 Unit  | <b>DJOOW++</b><br>2-Port<br>106 Duplex<br>Frame<br>Office White     | <b>HBL2610</b><br>30A 125V<br>Twist-Lock<br>Receptacle<br>(1.56" boss<br>diameter)<br>Black  |
|                                                                                                                                                                                                                                                        | <b>SISTOW**</b><br>ST-Style<br>Adapter<br>Office White                    | <b>DFRA2KOW</b><br>2-Port<br>Keystone<br>Recessed<br>1.5 Unit  | <b>DJ106OW++</b><br>4-Port<br>106 Duplex<br>Frame<br>Office White   | <b>HBL2620</b><br>30A 250V<br>Twist-Lock<br>Receptacle<br>(1.56" boss<br>diameter)<br>Black  |
|                                                                                                                                                                                                                                                        |                                                                                                                                                              | <b>DF115FFOW</b><br>15-Pin SVGA<br>F/F, 1 Unit                 |                                                                                                                                                          |                                                                                                                                                                                   |
|                                                                                                                                                                                                                                                        |                                                                                                                                                              | <b>DF19FFOW</b><br>9-Pin F/F<br>1 Unit                         |                                                                                                                                                          |                                                                                                                                                                                   |
|                                                                                                                                                                                                                                                        |                                                                                                                                                              | <b>DF115SOW</b><br>15-Pin SVGA<br>Screw Terminal<br>1 Unit     |                                                                                                                                                          |                                                                                                                                                                                   |

Extron is a registered trademark of Extron Electronics.  
 Krone is a registered trademark of Krone, Inc.  
 MAX and CT Series are registered trademarks of The Siemon Company.  
 Mini-Com and Panduit are registered trademarks of Panduit Corp.  
 NORDX is a registered trademark of Belden/CDT, Inc.  
 SYSTIMAX is a registered trademark of CommScope, Inc.  
 TracJack, Series II and Ortronics are registered trademarks of Ortronics/Legrand.