

SPECIFICATION CONTROL DRAWING

55PC0213

TITLE WIRE, RADIATION-CROSSLINKED, MODIFIED ETFE-INSULATED, MEDIUM WEIGHT, GENERAL PURPOSE, 600 VOLT


Date 2-1-10

Revision F

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.

CONDUCTOR - NICKEL-COATED COPPER

INSULATION - RADIATION - CROSSLINKED,
MODIFIED ETFE



CONSTRUCTION DETAILS

PART NUMBER <u>1/</u>	WIRE SIZE (AWG)	CONDUCTOR STRANDING (number x AWG)	CONDUCTOR DIAMETER (in.)			FINISHED WIRE					
			LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	MAXIMUM RESISTANCE AT 20°C (ohms/1000 ft.)	DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
							LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC0213-26-*	26	19 x 38	.0175	.0183	.0191	42.2	.0328	.0345	.0362	1.38	1.52
55PC0213-24-*	24	19 x 36	.0225	.0233	.0241	25.9	.0378	.0395	.0412	1.98	2.13
55PC0213-22-*	22	19 x 34	.0285	.0293	.0301	16.0	.0438	.0455	.0472	2.90	3.06
55PC0213-20-*	20	19 x 32	.0365	.0375	.0385	9.77	.0523	.0540	.0557	4.38	4.57
55PC0213-18-*	18	19 x 30	.0452	.0464	.0476	6.10	.0616	.0635	.0654	6.59	6.90
55PC0213-16-*	16	19 x 29	.0514	.0527	.0538	4.76	.0690	.0710	.0730	8.37	8.70
55PC0213-14-*	14	19 x 27	.0644	.0659	.0674	3.00	.0838	.0860	.0882	12.88	13.33
55PC0213-12-*	12	37 x 28	.0825	.0845	.0865	1.98	.1020	.1047	.1074	19.73	20.30
55PC0213-10-*	10	37 x 26	.1050	.1070	.1090	1.24	.1252	.1290	.1328	31.12	32.13
55PC0213-8-*	8	133 x 29	.158	.163	.169	.694	.188	.196	.203	56.8	59.9
55PC0213-6-*	6	133 x 27	.198	.205	.212	.436	.233	.242	.251	89.7	94.7
55PC0213-4-*	4	133 x 25	.250	.260	.268	.275	.300	.311	.322	146.	154.
55PC0213-2-*	2	665 x 30	.320	.330	.340	.177	.370	.383	.397	227.	240.
55PC0213-1-*	1	817 x 30	.360	.370	.380	.144	.410	.424	.438	278.	291.
55PC0213-0-*	0	1045 x 30	.395	.415	.425	.113	.449	.466	.483	343.	366.
55PC0213-00-*	00	1330 x 30	.440	.462	.475	.089	.505	.525	.545	450.	481.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

The TE logo, Tyco Electronics and Raychem are trademarks.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable
501 Oakside Avenue
Redwood City, CA 94063-3800
Phone: 1-800-227-8816
Fax: 1-650-361-6297

WIRE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

COLOR: White preferred

CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour

IDENTIFICATION AND COLOR STRIPING DURABILITY:

125 cycles (250 strokes) (minimum). 500 g weight.

INSULATION ELONGATION AND TENSILE STRENGTH:

Total Insulation,

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

INSULATION FLAWS:

Spark Test, 3.0 kV (rms)

Impulse Dielectric Test, 8.0 kV (peak)

INSULATION THICKNESS: .008 in. (nominal) total insulation

SHRINKAGE: 230 ± 3°C for 1 hour, 0.125 inch (maximum) in 12 inches.

VOLTAGE WITHSTAND TEST (Post Environmental): 2500 volts (rms)

PART NUMBER:

The “*” in the part numbers on page 1 shall be replaced by a color code designator,

1/ Example: AWG 22, white: 55PC0213-22-9

AWG 22, white with black stripe: 55PC0213-22-90

1/ See footer section on page 1