

TWO HOLE HYLUG™ CODE CONDUCTOR STANDARD BARREL (Continued)





Fig. 1




Fig. 2




Fig. 3

C-44

Catalog Number	Fig #	Conductor		Stud Hole Size	Stud Hole Spacing	Tongue Width	Figure Dimensions		Dieless (# of crimps)	▲ Installation Tooling						Wire Strip Length	
		AWG	*** MM ²				(B)	(T)		(L)	Dieless (# of crimps)	Mechanical	Hydraulic		Color Code		Die Index
												MD6, OUR840, MD7-34R	BCT500HS, Y500CTHS	Y35, Y39, Y750, Y46*, PAT750			
YA6C-2L	1	6 AWG	-	1/4"	5/8"	.45"	.54"	.08"	2.01"	Y1MR (1) Y2MR (1) MY29-3 (1) MY29-11 (1) MRC840 (1)	W5CVT (1) W5CRT (1) X5CRT (1) X8CART (1)	W5CVT (1) W5CRT (1) X5CRT (1) X8CART (1)	U5CRT (1) U8CABT (1)	Blue	7	7/8"	
YA6C-2L-45	2							1.98"									
YA6C-2L-90	3							1.45"									
YA6C-2LN	1							3.87"									
YA6C-2LN-45	2			1/2"	1-3/4"	.81"		.12"	3.91"								
YA6C-2LN-90	3								3.28"								
YA6CL-2TC10	1								1.94"								
YA6CL-2TC10-45	2			# 10	5/8"	.42"		.09"	1.94"								
YA6CL-2TC10-90	3								1.39"								
YA6CL-2TC14	1								2.07"								
YA6CL-2TC14-45	2			1/4"	5/8"	.45"		.08"	2.04"								
YA6CL-2TC14-90	3								1.51"								
YA6CL-2TC14E	1								1.94"								
YA6CL-2TC14E-45	2			1/4"	1/2"	.45"		.08"	1.91"								
YA6CL-2TC14E-90	3								1.38"								
YA6CL-2TC14E1	1								2.44"								
YA6CL-2TC14E1-45	2			1/4"	1"	.45"		.08"	2.41"								
YA6CL-2TC14E1-90	3								1.88"								
YA6CL-2TC14E2	1								2.19"								
YA6CL-2TC14E2-45	2			1/4"	3/4"	.44"		.08"	2.16"								
YA6CL-2TC14E2-90	3								1.63"								
YA6CL-2TC38	1								2.63"								
YA6CL-2TC38-45	2			3/8"	1"	.63"		.06"	2.56"								
YA6CL-2TC38-90	3								2.06"								
YA6C-2L51	1								1.79"								
YA6C-2L51-45	2			# 10	1/2"	.42"		.09"	1.78"								
YA6C-2L51-90	3								1.23"								
YA6CL-2TC516	1								2.51"								
YA6CL-2TC516-45	2			5/16"	1"	.52"		.07"	2.45"								
YA6CL-2TC516-90	3								1.94"								
YA6CL-2TC516E2	1								2.26"								
YA6CL-2TC516E2-45	2			5/16"	3/4"	.52"		.07"	2.20"								
YA6CL-2TC516E2-90	3								1.69"								
YA6C-2L52	1								1.88"								
YA6C-2L52-45	2			1/4"	1/2"	.45"		.08"	1.85"								
YA6C-2L52-90	3								1.32"								
YA5C-2L	1	5 AWG					.81"	.07"	2.28"	Y1MR (2) Y2MR (2) MY29-3 (1) MY29-11 (1) MRC840 (1) Y644M (1)	W4CVT (1) W4CRT (1) X4CRT (1)	W4CVT (1) W4CRT (1) X4CRT (1)	U4CRT (1) U6CABT (1)	Gray	8	7/8"	
YA5C-2L-45	2			1/4"	5/8"	.44"			2.15"								
YA5C-2L-90	3								1.44"								
YA4C-2L	1	4 AWG	-				.81"	.09"	2.30"								
YA4C-2L-45	2			1/4"	5/8"	.49"			2.21"								
YA4C-2L-90	3								1.48"								
YA4CL-2TC14	1								2.36"								
YA4CL-2TC14-45	2			1/4"	5/8"	.49"		.81"	.09"								2.27"
YA4CL-2TC14-90	3								1.54"								
YA4CL-2TC38	1								2.96"								
YA4CL-2TC38-45	2			3/8"	1"	.58"		.81"	.08"								2.82"
YA4CL-2TC38-90	3								2.09"								
YA4CL-2TC14E1	1								2.74"								
YA4CL-2TC14E1-45	2			1/4"	1"	.49"		.81"	.09"								2.65"
YA4CL-2TC14E1-90	3								1.91"								

-- Color code not assigned.
▲ See tooling section of this catalog for complete tool and die listings.

◆ For applications greater than 2000 volts consult cable manufacturer for voltage stress relief instructions.
* Use PUADP-1 adapter with "U" dies in Y46 HYPRESS™.

** P-RT die sets for use in Y46 HYPRESS™ only, PUADP-1 adapter not required.
*** The MM² conductor sizes listed are the recommendations for Class 2 conductor.