

5

4

3

2




1

D

C


B

A




SPECIFICATIONS	
Mating cycles	500
Filter type	C
Capacitance	$3900 \text{ pF} \pm 20\%$
Working voltage	100 V
Current rating	7,5 A
Insulation resistance	$>1 \text{ G}\Omega$

FREQUENCY (MHz)	ATTENUATION (dB)
5	6
10	11
50	25
100	35
500	35
1000	32



PCB Layout, component side, thickness 1,6 mm

Mod.	Dat.	Name	Detail.	Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, female, angled, 37 poles, turned solder pins, screw locks and brackets with board locks	Maßstab/ Scale 1,5:1	Blatt/ Page 2 / 4
35300	01/12/08	PK	Insp.	08/07/02	CV				
33800	16/08/06	PK	Stand.						
32236	13/10/04	TR							
31058	08/07/02	CV					TB 09 64 414 724X		

09 64 414 7245	M3
09 64 414 7244	4-40 UNC-2B
Part number	Screw lock thread